



Actinic BL TL(-K) / TL-D(-K)

Actinic BL TL 11W/10

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap-Base	G5	Power Consumption	11.5 W
Useful Life (Nom)	2,000 hour(s)	Lamp Current (Nom)	0.400 A
Light Technical		Voltage (Nom)	34 V
Color Code	10	Mechanical and Housing	
Color Designation	Actinic	Bulb Shape	T16
Chromaticity Coordinate X (Nom)	230	Net Weight (Piece)	21.000 g
Chromaticity Coordinate Y (Nom)	230	Approval and Application	
UV Depreciation at 1000 h	40 %	Mercury (Hg) Content (Nom)	4.4 mg
UV Depreciation at 2000 h	45 %	CE mark	Yes
UV Depreciation at 500 h	30 %		


Actinic BL TL(-K) / TL-D(-K)

UV	
UV-A Radiation 100Hr (IEC)	2.0 W

Product Data	
Order product name	Actinic BL TL 11W/10
Full product name	Actinic BL TL 11W/10
Full product code	871150095145827
Order code	928000601030


Material Nr. (12NC)	928000601030
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500951458
Numerator - Packs per outer box	250
EAN/UPC - Case	8711500951472

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 11W/10	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm

Photometric data



Spectral Power Distribution Colour - Actinic BL TL 11W/10

