



Blue (/52) TL/TL-D

TL 20W/52 SLV/25

By emitting light almost entirely within the 400 to 500 nm bandwidth and peaking at 450 nm, Philips TL/TL-D color 52 lamps have no radiation from the short wave UVB. waveband. They are therefore suitable to be used in systems for applications such as Agriculture and Neonatal Jaundice Phototherapy

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take them to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	No
Life to 50% Failures (Nom)	9,000 hour(s)		
Useful Life (Nom)	2,000 hour(s)	Mechanical and Housing	
		Bulb Shape	T38
		Net Weight (Piece)	156.000 g
Light Technical		Approval and Application	
Color Code	52	Mercury (Hg) Content (Nom)	8.0 mg
Luminous Flux	318 lm	CE mark	Yes
Chromaticity Coordinate X (Nom)	154		
Chromaticity Coordinate Y (Nom)	69	Product Data	
Operating and Electrical		Order product name	TL 20W/52 SLV/25
Power Consumption	19.3 W	Full product name	TL 20W/52 SLV/25
Lamp Current (Nom)	0.36 A	Full product code	871150064302540
Voltage (Nom)	59 V	Order code	928003505203
		Material Nr. (12NC)	928003505203
		Numerator - Quantity Per Pack	1

Blue (/52) TL/TL-D


EAN/UPC - Product/Case	8711500643025
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500643032

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 20W/52 SLV/25	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data



Spectral Power Distribution Colour - TL 20W/52 SLV/25

