



Flexo Print

TL 60W/10-R SLV/25

Flexo print TL lamps emit almost all of their light (99.9%) in the useful UVA and visible blue wavebands – between 350 and 400 nm – and have peak intensity at 370 nm (except for the /03 version). This makes them ideal for flexo printing equipment and photopolymerization processes. In addition, the 'R' lamps in the family have an internal 200-degree reflector to further optimize the lamp's overall efficiency.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Lamp Current (Nom)		0.7 A
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Voltage (Nom)	102 V	
Life to 50% Failures (Nom)	2,000 hour(s)	Mechanical and Housing		
Useful Life (Nom)	1,000 hour(s)	Bulb Shape	T38	
Light Technical		Net Weight (Piece)	260.200 g	
Color Code	10-R	Approval and Application		
Color Designation	Ultra Violet A	Mercury (Hg) Content (Nom)	13.0 mg	
Chromaticity Coordinate X (Nom)	222	CE mark	Yes	
Chromaticity Coordinate Y (Nom)	210	UV		
UV Depreciation at 1000 h	15 %	UV-A Radiation 100Hr (IEC)	15.8 W	
UV Depreciation at 2000 h	30 %	Product Data		
UV Depreciation at 500 h	10 %	Order product name	TL 60W/10-R SLV/25	
Operating and Electrical				
Power Consumption	62 W			

Flexo Print

Full product name	TL 60W/10-R SLV/25
Full product code	871150061572540
Order code	928008401003
Material Nr. (12NC)	928008401003
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500615725
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500615732

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 60W/10-R SLV/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm



Photometric data



Spectral Power Distribution Colour - TL 60W/10-R SLV/25

