



MASTER Actinic BL TL-D Secura

MASTER Actinic BL TL-D 15W/10 Secura

The Philips MASTER Actinic BL TL-D Secura family combines multiple benefits in one lamp. These lamps have the perfect spectrum for attracting insects. Also, they have virtually no UV-B output, and so are perfectly safe. Furthermore, they have the special "MASTER" coating to improve the efficiency, initial UV-A output and maintenance of the lamp. And finally, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, combined with their high efficiency, these lamps represent the best choice for the environment.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | | UV Depreciation at 2000 h | | 7 % | |
|---------------------------------|---------------------------------|---------------------------|--|---------------------------|------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] | UV Depreciation at 5000 h | | UV Depreciation at 8000 h | 18 % |
| Life to 50% Failures (Nom) | 13,000 hour(s) | | | | |
| Useful Life (Nom) | 12,000 hour(s) | | | | |
| Light Technical | | Operating and Electrical | | | |
| Color Code | 10 | Power Consumption | | 15.5 W | |
| Color Designation | Actinic | Lamp Current (Nom) | | 0.335 A | |
| Chromaticity Coordinate X (Nom) | 225 | Voltage (Nom) | | 55 V | |
| Chromaticity Coordinate Y (Nom) | 215 | | | | |

MASTER Actinic BL TL-D Secura

| Mechanical and Housing | |
|----------------------------|--------------------------------------|
| Bulb Shape | T26 |
| Net Weight (Piece) | 86.900 g |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 3.0 mg |
| UV | |
| UV-A Radiation 100Hr (IEC) | 3.15 W |
| Product Data | |
| Order product name | MASTER Actinic BL TL-D 15W/10 Secura |


| | |
|---------------------------------|--------------------------------------|
| Full product name | MASTER Actinic BL TL-D 15W/10 Secura |
| Full product code | 871829119608200 |
| Order code | 19608200 |
| Material Nr. (12NC) | 928022701003 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291196082 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 8718291196099 |

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|--------------------------------------|---------|----------|----------|----------|----------|
| MASTER Actinic BL TL-D 15W/10 Secura | 28 mm | 437.4 mm | 444.5 mm | 442.1 mm | 451.6 mm |

Photometric data



Spectral Power Distribution Colour - MASTER Actinic BL TL-D 15W/10 Secura

MASTER Actinic BL TL-D Secura

