



Actinic BL TL(-K) / TL-D(-K)

Actinic BL TL-D 15W/10 1SL/25

Tubular low-pressure mercury vapour fluorescent lamps

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T26
Life to 50% Failures (Nom)	8,000 hour(s)	Net Weight (Piece)	56.570 g
Useful Life (Nom)	9,000 hour(s)		
Light Technical		Approval and Application	
Color Code	10	Mercury (Hg) Content (Nom)	5.0 mg
Color Designation	Actinic	CE mark	Yes
Chromaticity Coordinate X (Nom)	222	UV	
Chromaticity Coordinate Y (Nom)	210	UV-A Radiation 100Hr (IEC)	3.9 W
UV Depreciation at 2000 h	10 %		
UV Depreciation at 5000 h	15 %	Product Data	
UV Depreciation at 8000 h	20 %	Order product name	Actinic BL TL-D 15W/10 1SL/25
Operating and Electrical		Full product name	Actinic BL TL-D 15W/10 1SL/25
Power Consumption	15 W	Full product code	871150071093240
Lamp Current (Nom)	0.34 A	Order code	928024801029
Voltage (Nom)	55 V	Material Nr. (12NC)	928024801029
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500710932

Actinic BL TL(-K) / TL-D(-K)


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500710949

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm



Photometric data



Spectral Power Distribution Colour - Actinic BL TL-D 15W/10 1SL/25

