



MASTER TL-D Food

MASTER TL-D Food 30W/79 SLV/25

The TL-D Food lamp makes the appearance of meat and bakery products more fresh and tasty. It can be applied for food illumination in butcher shops, bakeries, supermarkets etc.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	15.000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	79	Bulb Shape	T8
Luminous Flux	1,300 lm	Net Weight (Piece)	113.000 g
Color Designation	Food		
Correlated Color Temperature (Nom)	3800 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	43 lm/W	Mercury (Hg) Content (Nom)	5.0 mg
Color rendering index (CRI)	74	Energy Consumption kWh/1000 h	37 kWh
Operating and Electrical		Product Data	
Power Consumption	30.0 W	Order product name	MASTER TL-D Food 30W/79 SLV/25
Lamp Current (Nom)	0.360 A	Full product name	MASTER TL-D Food 30W/79 SLV/25
Voltage (Nom)	98 V	Full product code	871150070624940
		Order code	928025402043
		Material Nr. (12NC)	928025402043
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500706249

MASTER TL-D Food


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500613103

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Food 30W/79 SLV/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Food 30W/79 SLV/25

Lifetime




Life expectancy diagram - 12 hour cycle



Life expectancy diagram - 3 hour cycle

MASTER TL-D Food

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Food 30W/79 SLV/25

