



MASTER TL-E Circular Super 80



TL-E 22W/865 1CT/12

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	G10q	Power Consumption	22.2 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.400 A
Life to 50% Failures (Nom)	13,000 hour(s)	Voltage (Nom)	62 V
Light Technical		Controls and Dimming	
Color Code	865 [CCT of 6500K]	Dimmable	Yes
Luminous Flux	1,250 lm	Mechanical and Housing	
Color Designation	Cool Daylight	Bulb Shape	C-T29
Chromaticity Coordinate X (Nom)	0.313	Net Weight (Piece)	0.110 kg
Chromaticity Coordinate Y (Nom)	0.337	Approval and Application	
Correlated Color Temperature (Nom)	6500 K	Energy Efficiency Class	G
Luminous Efficacy (rated) (Nom)	57 lm/W	Mercury (Hg) Content (Max)	8 mg
Color rendering index (CRI)	80	Mercury (Hg) Content (Nom)	8 mg

MASTER TL-E Circular Super 80

Energy Consumption kWh/1000 h	23 kWh
EPREL Registration Number	423507
Product Data	
Order product name	TL-E 22W/865 1CT/12
Full product name	TL-E 22W/865 1CT/12
Full product code	872790084053700
Order code	928026286570

Material Nr. (12NC)	928026286570
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900840537
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900840544

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 22W/865 1CT/12	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm

