



UVB Broadband TL

TL 100W/12 SLV/10

The UVB Broadband TL lamps emit radiation in the 'B' bandwidth of the UV spectrum (290 to 315 nm) . This make these lamps suitable for various applications such as photo-therapy, agriculture & curing

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Photobiological Safety – IEC 62471 - Risk Group 3. WARNING - UV is emitted from these products.


Product data

General Information		Mechanical and Housing	
Cap-Base	R17d (RDC)	Bulb Shape	T38
Life to 50% Failures (Nom)	1,000 hour(s)	Net Weight (Piece)	410.000 g
Useful Life (Nom)	1,000 hour(s)		
Light Technical		Approval and Application	
Color Code	12	Mercury (Hg) Content (Nom)	14.0 mg
Color Designation	Ultra Violet B		
Chromaticity Coordinate X (Nom)	240	UV	
Chromaticity Coordinate Y (Nom)	250	UV-B Radiation 100 hr (IEC)	13.5 W
UV Depreciation at 1000 h	15 %	UV-B Radiation 5hr (IEC)	14.3 W
UV Depreciation at 500 h	10 %		
Operating and Electrical		Product Data	
Power Consumption	100 W	Order product name	TL 100W/12 SLV/10
Lamp Current (Nom)	0.97 A	Full product name	TL 100W/12 SLV/10
Voltage (Nom)	126 V	Full product code	871869666241000
		Order code	928034901230
		Material Nr. (12NC)	928034901230
		Numerator - Quantity Per Pack	1

UVB Broadband TL


EAN/UPC - Product/Case	8718696662410
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696662427

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 100W/12 SLV/10	40.5 mm	1,763.8 mm	1,770.9 mm	1,768.5 mm	1,782.2 mm

Photometric data



Spectral Power Distribution Colour - TL 100W/12 SLV/10

