



Actinic BL TL(-K) / TL-D(-K)

Actinic BL TL-D 25W/10 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Lamp Current (Nom)	0.612 A
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Voltage (Nom)	48 V
Nominal lifetime	8,000 hour(s)	Mechanical and Housing	
Life to 50% Failures (Nom)	8,000 hour(s)	Bulb Shape	T26
Useful Life (Nom)	5,000 hour(s)	Net Weight (Piece)	0.057 kg
Light Technical		Approval and Application	
Color Code	10	Mercury (Hg) Content (Nom)	5 mg
Chromaticity Coordinate X (Nom)	225	UV	
Chromaticity Coordinate Y (Nom)	230	UV-A Radiation 100Hr (IEC)	5.4 W
Operating and Electrical			
Power Consumption	25 W		

Actinic BL TL(-K) / TL-D(-K)


Product Data

Order product name	Actinic BL TL-D 25W/10 1SL/25
Full product name	Actinic BL TL-D 25W/10 1SL/25
Full product code	872016930678300
Order code	928039401015
Material Nr. (12NC)	928039401015


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169306783
Numerator - Packs per outer box	25
EAN/UPC - Case	8720169306790

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 25W/10 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm



Photometric data



Spectral Power Distribution Colour - Actinic BL TL-D 25W/10 1SL/25

