



# TL-D Standard Colours

## TL-D 18W/33-640 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	13,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	33-640	Bulb Shape	T8
Luminous Flux	1,200 lm	Net Weight (Piece)	71.000 g
Color Designation	Cool White (CW)		
Correlated Color Temperature (Nom)	4100 K	Approval and Application	
Color rendering index (CRI)	63	Mercury (Hg) Content (Nom)	5.0 mg
		Energy Consumption kWh/1000 h	22 kWh
Operating and Electrical		Product Data	
Power Consumption	18.0 W	Order product name	TL-D 18W/33-640 1SL/25
Lamp Current (Nom)	0.360 A	Full product name	TL-D 18W/33-640 1SL/25
Voltage (Nom)	59 V	Full product code	871150095041340
		Order code	928048003312
		Material Nr. (12NC)	928048003312
		Numerator - Quantity Per Pack	1

# TL-D Standard Colours


EAN/UPC - Product/Case	8711500950413
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500950420

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/33-640 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

## Photometric data




Spectral Power Distribution Colour - TL-D 18W/33-640 1SL/25

## Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

## TL-D Standard Colours

### Lifetime



Lumen Maintenance Diagram - TL-D 18W/33-640 1SL/25

