



TUV T8

TUV TL-D 95W HO SLV/25

TUV T8 lamps are double-ended UV-C 253.7 nm emitting lamps. TUV T8 lamps offer almost constant UV-C output over their complete lifetime. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

Product data


General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T26
Useful Life (Nom)	8,000 hour(s)	Net Weight (Piece)	233.000 g
Light Technical		Approval and Application	
Color Code	TUV	Mercury (Hg) Content (Nom)	8.0 mg
Color Designation	- [Not Specified]	CE mark	Yes
Depreciation at Useful Lifetime	15 %		
Operating and Electrical		UV	
Power Consumption	60 W	UV-C Radiation at 100 hr	22.5 W
Lamp Current (Nom)	0.620 A		
Voltage (Nom)	124 V		
Product Data			
Order product name	TUV TL-D 95W HO SLV/25		
Full product name	TUV TL-D 95W HO SLV/25		
Full product code	871150089392540		

TUV T8

Order code	928049804006
Material Nr. (12NC)	928049804006
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500893925

Numerator - Packs per outer box	25
EAN/UPC - Case	8711500893932

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV TL-D 95W HO SLV/25	28 mm	1,500 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data



Spectral Power Distribution Colour - TUV TL-D 95W HO SLV/25

