



MASTER MHN-LA 複金屬燈

MASTER MHN-LA 1000W/842 230V XWH

雙封式袖珍型石英複金屬燈

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	X528
操作位置	P5 [平行 +/-5D 或水平 (HOR)]
壽命 (故障率 50%) (標稱)	15,000 h

照明技術	
色碼	842 [CCT of 4200K]
色彩名稱	冷白光 (CW)
色度坐標 X (標稱)	366
色度坐標 Y (Nom)	370
相關色溫 (標稱)	4200 K
光效 (額定) (標準)	92.00 lm/W
演色性指數 (CRI)	70
電弧長 O (標稱)	40.5 mm

運轉與電力	
耗電量	1,040.0 W

電壓 (標稱)	125 V
---------	-------

控制與調光	
可調光	否

機械與外罩	
燈泡表層	透明
燈泡形狀	TD40
淨重 (個)	141.000 g

認證與應用	
汞 (Hg) 含量 (標稱)	112 mg
能源消耗 kWh/1000 h	1,144 kWh
CE 標誌	是


產品資料	
下訂產品名稱	MASTER MHN-LA 1000W/842 230V XWH

MASTER MHN-LA 複金屬燈

完整產品名稱	MASTER MHN-LA 1000W/842 230V XWH
完整產品代碼	871150020078500
訂單代碼	928073005130
材質 Nr. (12NC)	928073005130
分子 - 每個包裝的數量	1


EAN/UPC - 產品/案例	8718291548232
分子 - 每一外盒包裝	1
EAN/UPC - 箱	8711500200785

二维绘图




Product	D (max)	O	X	A
MASTER MHN-LA 1000W/842 230V XWH	40 mm	40.5 mm	35 mm	286 mm

光度数据




Spectral Power Distribution Colour - MASTER MHN-LA 1000W/842 230V XWH

壽命



LDLE_MHN-LA_0001-Life expectancy diagram



Lumen Maintenance Diagram - MASTER MHN-LA 1000W/842 230V XWH

MASTER MHN-LA 複金屬燈

