



Architectural MSD

MSD 575 1CT/16

The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	GX9.5
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	3,000 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux	43,000 lm
Chromaticity Coordinate X (Nom)	323
Chromaticity Coordinate Y (Nom)	317
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (Rated) (Min)	68 lm/W
Luminous Efficacy (rated) (Nom)	75 lm/W
Color rendering index (CRI)	72
Arc Length O (Nom)	8.0 mm
Operating and Electrical	
Power Consumption	575 W

Lamp Current (Nom)	7.6 A
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Net Weight (Piece)	0.062 kg
Approval and Application	
CE mark	Yes
Product Data	
Order product name	MSD 575 1CT/16
Full product name	MSD 575 1CT/16
Full product code	872790091755000
Order code	928098805114
Material Nr. (12NC)	928098805114
Numerator - Quantity Per Pack	1

Architectural MSD


EAN/UPC - Product/Case	8727900917550
Numerator - Packs per outer box	16
EAN/UPC - Case	8727900917567

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD 575	30 mm	8.0	64 mm	66 mm	65	125 mm	36 mm	35	34 mm
1CT/16		mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSD 575 1CT/16

