



Architectural MSD

MSD 575 1CT/16

The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Lamp Current (Nom)	
Cap-Base	GX9.5		7.6 A
Operating Position	UNIVERSAL [Any or Universal (U)]	Controls and Dimming	
Life to 50% Failures (Nom)	3,000 hour(s)	Dimmable	No
Light Technical		Mechanical and Housing	
Color Code	- [Not Specified]	Net Weight (Piece)	0.062 kg
Luminous Flux	43,000 lm	Approval and Application	
Chromaticity Coordinate X (Nom)	323	CE mark	Yes
Chromaticity Coordinate Y (Nom)	317	Product Data	
Correlated Color Temperature (Nom)	6000 K	Order product name	MSD 575 1CT/16
Luminous Efficacy (Rated) (Min)	68 lm/W	Full product name	MSD 575 1CT/16
Luminous Efficacy (rated) (Nom)	75 lm/W	Full product code	872790091755000
Color rendering index (CRI)	72	Order code	91755000
Arc Length O (Nom)	8.0 mm	Material Nr. (12NC)	928098805114
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	575 W		

Architectural MSD


EAN/UPC - Product/Case	8727900917550
Numerator - Packs per outer box	16
EAN/UPC - Case	8727900917567

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD 575	30 mm	8.0	64 mm	66 mm	65	125 mm	36 mm	35	34 mm
1CT/16		mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSD 575 1CT/16

