



Architectural MSD

MSD 575 1CT/16

The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

| General Information | | Lamp Current (Nom) | |
|------------------------------------|----------------------------------|-------------------------------|-----------------|
| Cap-Base | GX9.5 | | 7.6 A |
| Operating Position | UNIVERSAL [Any or Universal (U)] | Controls and Dimming | |
| Life to 50% Failures (Nom) | 3,000 hour(s) | Dimmable | No |
| Light Technical | | Mechanical and Housing | |
| Color Code | - [Not Specified] | Net Weight (Piece) | 0.062 kg |
| Luminous Flux | 43,000 lm | Approval and Application | |
| Chromaticity Coordinate X (Nom) | 323 | CE mark | Yes |
| Chromaticity Coordinate Y (Nom) | 317 | Product Data | |
| Correlated Color Temperature (Nom) | 6000 K | Order product name | MSD 575 1CT/16 |
| Luminous Efficacy (Rated) (Min) | 68 lm/W | Full product name | MSD 575 1CT/16 |
| Luminous Efficacy (rated) (Nom) | 75 lm/W | Full product code | 872790091755000 |
| Color rendering index (CRI) | 72 | Order code | 928098805114 |
| Arc Length O (Nom) | 8.0 mm | Material Nr. (12NC) | 928098805114 |
| Operating and Electrical | | Numerator - Quantity Per Pack | 1 |
| Power Consumption | 575 W | | |

Architectural MSD


| | |
|---------------------------------|---------------|
| EAN/UPC - Product/Case | 8727900917550 |
| Numerator - Packs per outer box | 16 |
| EAN/UPC - Case | 8727900917567 |

Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) | F (max) | F | F (min) |
|---------|---------|-----|---------|---------|----|---------|---------|----|---------|
| MSD 575 | 30 mm | 8.0 | 64 mm | 66 mm | 65 | 125 mm | 36 mm | 35 | 34 mm |
| 1CT/16 | | mm | | | mm | | | mm | |

Photometric data



Spectral Power Distribution Colour - MSD 575 1CT/16

