



Architectural MSD

MSD 575 HR 1CT/8

The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.


Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	G22		6.95 A
Operating Position	UNIVERSAL [Any or Universal (U)]	Controls and Dimming	
Life to 50% Failures (Nom)	2,000 hour(s)	Dimmable	No
Light Technical		Mechanical and Housing	
Color Code	- [Not Specified]	Net Weight (Piece)	0.094 kg
Luminous Flux	47,000 lm	Product Data	
Chromaticity Coordinate X (Nom)	328	Order product name	MSD 575 HR 1CT/8
Chromaticity Coordinate Y (Nom)	331	Full product name	MSD 575 HR 1CT/8
Correlated Color Temperature (Nom)	6000 K	Full product code	872790091648500
Luminous Efficacy (rated) (Nom)	81 lm/W	Order code	928098905114
Color rendering index (CRI)	75	Material Nr. (12NC)	928098905114
Arc Length O (Nom)	8.0 mm	Numerator - Quantity Per Pack	1
Operating and Electrical		EAN/UPC - Product/Case	8727900916485
Power Consumption	575 W	Numerator - Packs per outer box	8
		EAN/UPC - Case	8727900916492

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD 575	30 mm	8.0	69 mm	71 mm	70	145 mm	43 mm	42	41 mm
HR 1CT/8		mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSD 575 HR 1CT/8

