



Architectural MSD

MSD 700.1CT/3

The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.


Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	G22		11 A
Operating Position	UNIVERSAL [Any or Universal (U)]	Controls and Dimming	
Life to 50% Failures (Nom)	3,000 hour(s)	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	- [Not Specified]	Net Weight (Piece)	0.147 kg
Luminous Flux	49,000 lm	Product Data	
Chromaticity Coordinate X (Nom)	317	Order product name	MSD 700.1CT/3
Chromaticity Coordinate Y (Nom)	320	Full product name	MSD 700.1CT/3
Correlated Color Temperature (Nom)	5900 K	Full product code	872790091129900
Luminous Efficacy (rated) (Nom)	70 lm/W	Order code	928170405114
Color rendering index (CRI)	75	Material Nr. (12NC)	928170405114
Arc Length O (Nom)	10.0 mm	Numerator - Quantity Per Pack	1
Operating and Electrical		EAN/UPC - Product/Case	8727900911299
Power Consumption	700 W	Numerator - Packs per outer box	3
		EAN/UPC - Case	8727900911305

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD	40 mm	10.0	84 mm	86 mm	85	175 mm	54 mm	53	52 mm
700.1CT/3		mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSD 700.1CT/3

