



# MSR

## MSR 575/2 10H 1CT/4

MSR – bright vivid colours, always The high colour rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colours of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Arc Length O (Nom)	
Cap-Base	GX9.5		7.0 mm
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 50% Failures (Nom)	1,000 hour(s)	Power Consumption	575 W
		Lamp Current (Nom)	6.75 A
Light Technical		Controls and Dimming	
Color Code	2	Dimmable	No
Luminous Flux	47,000 lm	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	302	Net Weight (Piece)	0.057 kg
Chromaticity Coordinate Y (Nom)	320		
Correlated Color Temperature (Nom)	6990 K		
Luminous Efficacy (Rated) (Min)	75 lm/W		
Luminous Efficacy (rated) (Nom)	82 lm/W		
Color rendering index (CRI)	73		

# MSR

## Approval and Application


CE mark Yes

## Product Data

Order product name MSR 575/2 10H 1CT/4  
 Full product name MSR 575/2 10H 1CT/4  
 Full product code 871829122127200  
 Order code 928171605115


Material Nr. (12NC) 928171605115  
 Numerator - Quantity Per Pack 1  
 EAN/UPC - Product/Case 8718291221272  
 Numerator - Packs per outer box 4  
 EAN/UPC - Case 8718291221289

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575/2	30 mm	7.0	64 mm	66 mm	65	125 mm	36 mm	35	34 mm
10H 1CT/4		mm			mm			mm	

## Photometric data



Spectral Power Distribution Colour - MSR 575/2 10H 1CT/4

