



Architectural MSD

MSD 1200.1CT/3

Architectural MSD – single ended night colours The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent colour rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	G22		13.8 A
Operating Position	UNIVERSAL [Any or Universal (U)]	Controls and Dimming	
Life to 50% Failures (Nom)	2,000 hour(s)	Dimmable	No
Light Technical		Mechanical and Housing	
Color Code	- [Not Specified]	Net Weight (Piece)	0.156 kg
Luminous Flux	92,000 lm	Approval and Application	
Chromaticity Coordinate X (Nom)	323	CE mark	Yes
Chromaticity Coordinate Y (Nom)	328	Product Data	
Correlated Color Temperature (Nom)	6000 K	Order product name	MSD 1200.1CT/3
Luminous Efficacy (rated) (Nom)	79 lm/W	Full product name	MSD 1200.1CT/3
Color rendering index (CRI)	73	Full product code	872790091135000
Arc Length O (Nom)	14.0 mm	Order code	928172005114
Operating and Electrical		Material Nr. (12NC)	928172005114
Power Consumption	1,200 W		

Architectural MSD

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900911350
Numerator - Packs per outer box	3


EAN/UPC - Case	8727900911367
----------------	---------------

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD	42.5	14.0	84 mm	86 mm	85	183 mm	54 mm	53	52 mm
1200.1CT/3	mm	mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSD 1200.1CT/3

