



# MASTERColour CDM-Rm Elite Mini



## CDM-Rm Elite Mini 35W/930 GX10 MR16 40D

Mini, very high-efficiency Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high color rendering

### Warnings and Safety

- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035).
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information		Color rendering index (CRI)		90
Cap-Base	GX10	LLMF At End Of Nominal Lifetime (Nom)	80 %	
Operating Position	UNIVERSAL [Any or Universal (U)]	Luminous Flux in 90° Cone (Rated)	2,150 lm	
Switching Cycle	1,350	<b>Operating and Electrical</b>		
Flux measurement reference	Narrow Cone	Power Consumption	39.1 W	
Life to 50% Failures (Nom)	15,000 hour(s)	Warm-up time to 60% light	120 s	
<b>Light Technical</b>		Voltage (Nom)	87 V	
Color Code	930 [CCT of 3000K]	<b>Controls and Dimming</b>		
Beam Angle (Nom)	40 degree(s)	Dimmable	No	
Luminous Flux	2,150 lm	<b>Mechanical and Housing</b>		
Luminous Intensity (Nom)	3,600 cd	Bulb Shape	MR16	
Chromaticity Coordinate X (Nom)	0.434	Net Weight (Piece)	0.048 kg	
Chromaticity Coordinate Y (Nom)	0.398			
Correlated Color Temperature (Nom)	3000 K			
Luminous Efficacy (rated) (Nom)	61 lm/W			



# MASTERCcolour CDM-Rm Elite Mini

## Lifetime



LDLE\_CDM-Rm\_35W\_930-Life expectancy diagram

Lumen Maintenance Diagram - CDM-Rm Elite Mini 35W/930 GX10 MR16 40D

