



MASTER MHN-SA

MASTER MHN-SA 2000W/956 400V XW HO UNP/1

Compact quartz metal halide lamps with double-pinch

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	X830R
Operating position	P15 [Parallel +/-15D or Horizontal(HOR)]
Life to 50% failures (nom.)	5,000 h

Light Technical	
Colour Code	956 [CCT of 5600K]
Colour designation	Daylight
Chromaticity Coordinate X (Nom)	330
Chromaticity Coordinate Y (Nom)	366
Correlated Colour Temperature (Nom)	5600 K
Luminous efficacy (rated) (nom.)	108 lm/W
Colour rendering index (CRI)	81
Arc Length O (Nom)	25 mm

Operating and Electrical	
Power Consumption	2,100 W

Voltage (nom.)	
	205 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	TD40
Net Weight (Piece)	90,000 g

Approval and Application	
Mercury (Hg) content (nom.)	215 mg
Energy consumption kWh/1,000 hours	2,305 kWh
CE mark	Yes


Product Data	
Order product name	MASTER MHN-SA 2000W/956 400V XW HO UNP/1

MASTER MHN-SA

Full product name	MASTER MHN-SA 2000W/956 400V XW HO UNP/1
Full EOC	871829124183600
Order code	928195105129
Material no. (12 NC)	928195105129
Local order code	MHN-SA2000W


Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291548423
Numerator – packs per outer box	1
EAN/UPC - Case	8718291241836

Dimensional drawing




Product	D (max)	O	X	A	C (max)
MASTER MHN-SA 2000W/956 400V XW HO UNP/1	41 mm	25 mm	34 mm	226 mm	369 mm

Photometric data




Spectral Power Distribution Colour - MASTER MHN-SA 2000W/956 400V XW HO UNP/1

Lifetime



LDLE_MHN-SA_0006-Life expectancy diagram



Lumen Maintenance Diagram - MASTER MHN-SA 2000W/956 400V XW HO UNP/1

