



# MASTER MHN-SB

## MST MHN-SB 2000W/956 400V K12s-7 WH HO

Compact quartz metal halide lamp with single pinch

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Arc Length O (Nom)	
Cap-Base	Cable	25 mm	
Operating Position	P15 [Parallel +/-15D or Horizontal(HOR)]	Operating and Electrical	
Life to 50% Failures (Nom)	4,500 hour(s)	Power Consumption	2,100 W
Light Technical		Voltage (Nom)	205 V
Color Code	956 [CCT of 5600K]	Controls and Dimming	
Color Designation	Daylight	Dimmable	No
Chromaticity Coordinate X (Nom)	334	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	366	Bulb Finish	Clear
Correlated Color Temperature (Nom)	5600 K	Bulb Shape	TD40
Luminous Efficacy (rated) (Nom)	105 lm/W	Net Weight (Piece)	0.058 kg
Color rendering index (CRI)	81		

# MASTER MHN-SB

## Approval and Application


Mercury (Hg) Content (Nom)	215 mg
Energy Consumption kWh/1000 h	2,277 kWh
CE mark	Yes

## Product Data

Order product name	MST MHN-SB 2000W/956 400V K12s-7 WH HO
Full product name	MST MHN-SB 2000W/956 400V K12s-7 WH HO
Full product code	872790092860000


Order code	928196805130
Material Nr. (12NC)	928196805130
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291548454
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900928600

## Dimensional drawing



Product	D (max)	O	X	A	C (max)
MST MHN-SB 2000W/956 400V K12s-7 WH HO	41 mm	25 mm	50 mm	157 mm	188 mm



## Photometric data



Spectral Power Distribution Colour - MST MHN-SB 2000W/956 400V K12s-7 WH HO

# MASTER MHN-SB

## Lifetime



LDLE\_MHN-SB\_0002-Life expectancy diagram

Lumen Maintenance Diagram - MST MHN-SB 2000W/956 400V K12s-7 WH HO

