

CERTIFICATE

Issued to:
Applicant:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, The Netherlands

Licensee:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, The Netherlands

Product : Electronic driver for LED modules
Trade name(s) : PHILIPS
Type(s)/model(s) : XITANIUM 100W 0.70A Prog+ GL-Z sXt

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 61347-1:2015, EN 61347-2-13:2014, EN 61347-2-13:2014/A1:2017, EN 62384:2006 and EN 62384:2006/A1:2009
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 947556

DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration of the ENEC certification agreement and under the conditions of the ENEC certification agreement.

This certificate is issued on 21 November 2019 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-111263

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



A.C. Slingerland
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Electronic driver for LED modules
Trade name(s)	: PHILIPS
Type(s)/model(s)	: XITANIUM 100W 0.70A Prog+ GL-Z sXt
Rated input current	: 0,96 - 0,42 A
Rated input voltage/nature of supply	: 120 - 277 Vac
Rated input power	: 113 W
Rated frequency	: 50/60 Hz
Output current	: 100 - 700 mA
Output voltage range	: 72 - 143 V
Open circuit voltage max.	: 200 V
Power factor	: pf: 0,98...0,93
Max. case temperature	: tc: 80 °C
Description	: built-in LED driver

TESTS**Test requirements**

EN 61347-1:2015
EN 61347-2-13:2014
EN 61347-2-13:2014/A1:2017
EN 62384:2006
EN 62384:2006/A1:2009

Test result

The test results are laid down in DEKRA test file 224132200.

Additional information

The tests were performed by the manufacturer under the conditions of the agreement concerning the manufacturer's right to conduct type tests for the KEMA-KEUR / ENEC certification system under supervision of DEKRA (CTF Stage 3).

The isolation between primary and secondary is basic isolation
The isolation between primary / secondary and housing is double isolated

This certificate replaces certificate No. 2188185.01 which we herewith declare invalid.

The list of components is laid down at test report 2241322.52.

Conclusion

The examination proved that all requirements were met.

Factory location