

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

Electronic controlgear for LED modules

Name and address of the applicant

Signify Netherlands B.V.  
High Tech Campus 48, 5656 AE Eindhoven,  
Netherlands

Name and address of the manufacturer

Signify Netherlands B.V.  
High Tech Campus 48, 5656 AE Eindhoven,  
Netherlands

Name and address of the factory

*Note: When more than one factory, please report on page 2*☒ Additional information on page 2

Ratings and principal characteristics

Uin: 120-277 V; Freq.: 50/60 Hz; Iin: 0,39-0,17 A; Pin: 48 W;  
PF: 0,98-0,93C; Iout: 100-700 mA; Pout: 40 W;  
Output Voltage range: 29-57 V; Uout: 85 V max.;  
tc: 80 °C max.; SELV

Trademark / Brand (if any)

  
PHILIPS

Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

XITANIUM 40W 0.7A Prog+ GL-J sXt

Additional information (if necessary may also be reported on page 2)

This certificate replaces NL-66226 dated on 2020-06-15 due to technical modifications.

☐ Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016, IEC 62384:2020

National differences:

EU Group Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

6155053.50 and 6155053.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.  
Meander 1051  
Arnhem, 6825 MJ  
Netherlands

Date: 2023-05-18

Signature: Kate Xu

Additional factory

---

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.  
Meander 1051  
Arnhem, 6825 MJ  
Netherlands



Date: 2023-05-18

Signature: Kate Xu