

CERTIFICATE

Issued to:
Applicant:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, The Netherlands

Licensee:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, The Netherlands

Product : LED driver
Trade name(s) : PHILIPS
Type(s)/model(s) : Xi LP 75W 0.2-0.7A S1 230V S240 sXt, Xi LP 75W 0.5-1.5A S1 230V S240 sXt
and Xi LP 75W 0.3-1.0A S1 230V S240 sXt

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard(s) EN IEC 62384:2020, EN 61347-1:2015, EN 61347-1:2015/A1:2021, EN 61347-2-13:2014 and EN 61347-2-13:2014/A1:2017
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 947556

DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the ENEC certification agreement.

This certificate is issued on 20 October 2022 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 31-125821

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



K. Lin
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: LED driver
Trade name(s)	: PHILIPS
Type(s)/model(s)	: Xi LP 75W 0.2-0.7A S1 230V S240 sXt, Xi LP 75W 0.5-1.5A S1 230V S240 sXt and Xi LP 75W 0.3-1.0A S1 230V S240 sXt
Rated input voltage	: 220-240 Vac
Rated frequency	: 50/60 Hz
Rated input current	: 0,42-0,33 A
Rated input power	: 82 W
Rated output power	: 75 W
Rated maximum case temperature (tc)	: 85 °C
Ambient temperature range (ta)	: -40...+55 °C
Power factor (PF)	: 0,95
Description	: Built-in with double/reinforced insulation

Product data – type Xi LP 75W 0.3-1.0A S1 230V S240 sXt

Output current	: 300-1050 mA
Output voltage	: 35-108 V
Uout	: 140 Vdc

Product data – type Xi LP 75W 0.2-0.7A S1 230V S240 sXt

Output current	: 200-700 mA
Output voltage	: 50-150 V
Uout	: 190 Vdc

Product data – type Xi LP 75W 0.5-1.5A S1 230V S240 sXt

Output current	: 500-1500 mA
Output voltage	: 25-75 V
Uout	: 100 Vdc

TESTS**Test requirements**

EN IEC 62384:2020
EN 61347-1:2015
EN 61347-1:2015/A1:2021
EN 61347-2-13:2014
EN 61347-2-13:2014/A1:2017

Test result

The test results are laid down in DEKRA test file 614111800.

Additional information

constant current type
with screwless terminal
double insulation between PRI-SEC

The tests were performed by the manufacturer under the conditions of the agreement concerning the manufacturer's right to conduct type tests for the KEMA-KEUR / ENEC certification system under supervision of DEKRA (CTF Stage 3).

The list of components is laid down in test report 6141118.50.

Conclusion

The examination proved that all requirements were met.

Factory locations

The factory locations are registered with the numbers 674666, 306303, 312808 and 1845.