Ref. Certif. No.

NL-101232/M2

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Electronic controlgear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory *When more than one factory*	
Ratings and principal characteristics	**Product data** Ratings: Uin: 100-277 V; fn: 50/60 Hz; Iin: 0,14-0,39 A; Prated: 65 W; Irated: 0,7-2,0 Adc; Uoutput: 27-86 Vdc, Uout: 120 Vdc max ta: -40…+55 °C; Independent; PF: >0,9; IP66 (see General product information for explanation and range)
Trademark / Brand (if any)	PHILIPS, SIGNIFY, XITANIUM or ADVANCE
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Xi aP pW x-yA d WL Iz
Additional information	☒ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: EU Group Differences Comments: This CB test certificate replaces CB test certificate NL-101232/M1. Dated on 2025-07-23 due to technical modifications.
As shown in the Test Report Ref. No. which forms part of this Certificate	6270976.50 and 6270976.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-05-26

Signature: May Liu

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Additional factory

Additional information

Note:
Xi aP pW x-yA d WL Iz
a= Performance for driver, may be E (Eset tool).
p= maximum output power of the driver, maximum to 65.
x= Minimum adjustable output current of the driver by simple set, from 0,7 to 1,3, step per 0,01.
y= Maximum adjustable output current of the driver, from 1,05 to 2, step per 0,01.
d= Dimming function type, 1-10V or 5-0V for analog dimming function, blank for fixed output function.
z= 1-3 digits, size of the housing, from 90 to 112.

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-05-26

Signature: May Liu