



Classic LED spotMV

Essential LED 4.6-50W GU10 827 36D

LEDspot, PAR16, 50 W, GU10, 2700 K, 395 lm, 15000 hour(s)

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimize maintenance costs.

Product data

General Information	
Cap-Base	GU10
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	395 lm
Luminous Intensity (Nom)	700 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	85.90 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	4.6 W
Lamp Current (Nom)	39 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	78 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR16
Net Weight (Piece)	0.060 kg

Classic LED spotMV

Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
EU RoHS compliant	Yes

Application Conditions


Wireless Technology	Not applicable
---------------------	----------------

Product Data

Order product name	Essential LED 4.6-50W GU10 827 36D
--------------------	------------------------------------



Full product name	Essential LED 4.6-50W GU10 827 36D
Full product code	871869670059400
Order code	929001215208
Material Nr. (12NC)	929001215208
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696700594
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696700600

Dimensional drawing



Product	D	C
Essential LED 4.6-50W GU10 827 36D	50 mm	54 mm

Photometric data




Spectral Power Distribution Colour - Essential LED 4.6-50W GU10 827 36D

General uniform lighting - Essential LED 4.6-50W GU10 827 36D

Classic LED spotMV

Photometric data




Light Distribution Diagram - Essential LED 4.6-50W GU10 827 36D

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - Essential LED 4.6-50W GU10 827 36D

