



# CorePro LED spot MV

## Corepro LEDspot 4.6-50W GU10 865 36D

CorePro, LEDspot, PAR16, 50 W, GU10, 6500 K, 390 lm, CRI 80, 15000 hour(s)

CorePro, LEDspot, PAR16, 50 W, GU10, 6500 K, 390 lm, CRI 80, 15000 hour(s), 84.00 lm/W, EEL F, PF 0.5, Beam angle 36 degree(s), RG1, IP20, SVM 0.4, PstLM 1

### Product data

General Information	
Cap-Base	GU10
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Flux measurement reference	Narrow Cone
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	390 lm
Luminous Intensity (Nom)	770 cd
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	84.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	390 lm
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4.6 W
Lamp Current (Nom)	39 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	72 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR16
Net Weight (Piece)	0.045 kg

# CorePro LED spot MV

## Approval and Application

Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	391860
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


## Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

## Product Data



Order product name	Corepro LEDspot 4.6-50W GU10 865 36D
Full product name	Corepro LEDspot 4.6-50W GU10 865 36D
Full product code	871869672841300
Order code	929001218302
Material Nr. (12NC)	929001218302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696728413
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696728420

## Dimensional drawing



Product	D	C
Corepro LEDspot 4.6-50W GU10 865 36D	50 mm	54 mm

## Photometric data




Accent Lighting Spots - Corepro LEDspot 4.6-50W GU10 865 36D

Light Distribution Diagram - Corepro LEDspot 4.6-50W GU10 865 36D


# CorePro LED spot MV

## Photometric data




Spectral Power Distribution Colour - Corepro LEDspot 4.6-50W GU10 865 36D

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - Corepro LEDspot 4.6-50W GU10 865 36D

