



MASTER LED spot ExpertColor MV

MAS LED ExpertColor 3.9-35W GU10 940 25D

MASTER, LEDspot, PAR16, 35 W, GU10, 4000 K, 300 lm, CRI 97, 40000 hour(s), Glass

MASTER LEDspot ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. They offer superior lighting that has a customized spectrum, high CRI, and deep dimming feature. What's more the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, with MASTER LEDspot ExpertColor you can take advantage of the full ExpertColor family, which also includes LEDspot MR16, LEDspot AR111 and LEDspot PAR lamps. MASTER LEDspot ExpertColor delivers huge energy savings and minimizes maintenance costs without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within a short time period.

Product data

General Information	
Cap-Base	GU10
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Flux measurement reference	Narrow Cone
Light Technical	
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	300 lm

Luminous Intensity (Nom)	850 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	76 lm/W
Color Consistency	<3
Color rendering index (CRI)	97
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	300 lm
Photobiological safety according to EN 62471	RG1

MASTER LED spot ExpertColor MV

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	3.9 W
Lamp Current (Nom)	22 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V


Temperature	
T-Case Maximum (Nom)	56 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	PAR16
Net Weight (Piece)	0.038 kg

Approval and Application	
Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh

Dimensional drawing



EPREL Registration Number	391829
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C



Application Conditions	
can it be used in closed luminaires	No

Product Data	
Order product name	MAS LED ExpertColor 3.9-35W GU10 940 25D
Full product name	MAS LED ExpertColor 3.9-35W GU10 940 25D
Full product code	871869670753100
Order code	929001346602
Material Nr. (12NC)	929001346602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707531
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696707548

Product	D	C
MAS LED ExpertColor 3.9-35W GU10 940 25D	50 mm	54 mm


MASTER LED spot ExpertColor MV

Photometric data





Accent Lighting Spots - MAS LED ExpertColor 3.9-35W GU10 940 25D

Spectral Power Distribution Colour - MAS LED ExpertColor 3.9-35W GU10 940 25D



Light Distribution Diagram - MAS LED ExpertColor 3.9-35W GU10 940 25D

Lifetime



40K LED

Lumen Maintenance Diagram - MAS LED ExpertColor 3.9-35W GU10 940 25D

MASTER LED spot ExpertColor MV

