



MASTER VALUE LED spot MV

MAS LED spot VLE D 5-65W GU10 927 36D

LEDspot, PAR16, 65 W, GU10, 2700 K, 395 lm, 25000 hour(s)

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	GU10
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Warranty period	2 years

Light Technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	395 lm
Luminous Intensity (Nom)	650 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	79.00 lm/W

MASTER VALUE LED spot MV

Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	355 lm

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5 W
Lamp Current (Nom)	27 mA
Wattage Equivalent	65 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	65 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	PAR16
------------	-------

Net Weight (Piece)	0.041 kg
--------------------	----------

Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data

Order product name	MAS LED spot VLE D 5-65W GU10 927 36D
Full product name	MAS LED spot VLE D 5-65W GU10 927 36D
Full product code	871869975341200
Order code	929001348822
Material Nr. (12NC)	929001348822
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699753412
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699753429


Dimensional drawing




Product	D	C
MAS LED spot VLE D 5-65W GU10 927 36D	50 mm	54 mm

MASTER VALUE LED spot MV

Photometric data




General Parameters 4.1 Photo Lighting 8.1 Page 17





Accent Lighting Spots - MAS LED spot VLE D 5-65W GU10 927 36D

Spectral Power Distribution Colour - MAS LED spot VLE D 5-65W GU10 927 36D



Light Distribution Diagram - MAS LED spot VLE D 5-65W GU10 927 36D

Lifetime



25K LED

Lumen Maintenance Diagram - MAS LED spot VLE D 5-65W GU10 927 36D

MASTER VALUE LED spot MV

