



# MASTER VALUE LED spot MV

## Master LED 4.9-50W GU10 930 36D Dim

LEDspot, PAR16, 50 W, GU10, 3000 K, 405 lm, 25000 h

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information		Beam Angle (Nom)	
Cap-Base	GU10		36 degree(s)
Nominal lifetime	25,000 h	Luminous Flux	405 lm
Switching Cycle	50,000	Luminous Intensity (Nom)	650 cd
Lighting Technology	LEDspot	Color Designation	White (WH)
Light Technical		Correlated Color Temperature (Nom)	3000 K
Color Code	930 [CCT of 3000K]	Luminous Efficacy (rated) (Nom)	81.00 lm/W
		Color Consistency	<6
		Color rendering index (CRI)	90

# MASTER VALUE LED spot MV

LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	365 lm

## Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5 W
Lamp Current (Nom)	27 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

## Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Bulb Shape	PAR16
------------	-------

Net Weight (Piece)	0.038 kg
--------------------	----------


## Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C

## Product Data

Order product name	Master LED 4.9-50W GU10 930 36D Dim
Full product name	Master LED 4.9-50W GU10 930 36D Dim
Full product code	871869675592100
Local code description	M405L36D930GU10
Order code	929001348908
Material Nr. (12NC)	929001348908
Local order code	M405L36D930GU10
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696755921
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696755938


## Dimensional drawing




Product	D	C
Master LED 4.9-50W GU10 930 36D Dim	50 mm	54 mm

# MASTER VALUE LED spot MV

## Photometric data




© 2023 Philips Lighting B.V. Page 11





Accent Lighting Spots - Master LED 4.9-50W GU10 930 36D Dim

Spectral Power Distribution Colour - Master LED 4.9-50W GU10 930 36D Dim



Light Distribution Diagram - Master LED 4.9-50W GU10 930 36D Dim

## Lifetime



25K LED

Lumen Maintenance Diagram - Master LED 4.9-50W GU10 930 36D Dim

## MASTER VALUE LED spot MV

