

Xitanium LED drivers – spot- and downlight SELV Independent

Xitanium 50W WH 0.7-1.5A 54V Is G2
9290 014 71206

Enabling future-proof LED technology

Our Xitanium programmable window LED drivers ensure OEMs have complete flexibility and control in producing high quality luminaires. Available in application-dedicated form factors use and independent applications, our LED point drivers provide further customization via wide operating windows. Additionally, almost all drivers feature the following specifications: SELV, improved ripple current, temperature derating, – providing OEMs the tools to produce, and even alter later if necessary, premium downlights and spotlights.

Benefits

- High reliability underpinned by 5 year warranty
- Future-proof flexibility - application-oriented operating windows enable LED generation and complexity management
- Compatibility - can also be used for other manufacturers' modules or OEMs' own PCB designs

Application

- Retail
- Office

Features

- Operating windows - output current can be adjusted via the Philips MultiOne configurator ('TD' drivers) or with a resistor outside the driver or SimpleSet
- Power ratings: 10-75W
- Choice of housing designs -linear housing for tracks in '3 in 1' in design, conventional HID housings for down and Spotlighting and WH housing for independent use with strain relief and loop through

Logistical data

Specification item	Value
Product name	Xitanium 50W WH 0.7-1.5A 54V Is G2
EOC	871869961044900
Logistic code 12NC	9290 014 71206
EAN1 (GTIN)	8718699610449
EAN3 (box)	8718699610456
Pieces per box	20
Weight	217 gram

Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	220...240	V _{ac}	Performance range
Rated input voltage	230	V _{ac}	
Rated input frequency	50...60	Hz	Performance range
Rated input current	0.29	A	@ rated output power @ rated input voltage
Rated input power	60.0	W	@ rated output power @ rated input voltage
Power factor performance range	≥ 0.90 C		@ full output power @ rated input voltage@ rated output power @ rated input voltage
Total harmonic distortion	20	%	@ full output power @ rated input voltage
Efficiency	89.0	%	@ full output power @ rated input voltage @ max. I _{out}
Rated input voltage DC	186...250	V _{dc}	Performance range
Rated input current DC	≤ 0.32	A _{dc}	Performance range
Input voltage AC	198...264	V _{ac}	Operational range
Input frequency AC	45...66	Hz	Operational range
Input voltage DC	168...275	V _{dc}	Operational range
Isolation input to output	SELV		

Electrical output data


Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	24...54	V _{dc}	
Output voltage max.	60	V	Maximum output voltage (rms)
Output current	700...1500	mA	
Output current min programmable	700	mA	
Output current tolerance ±	5	%	@ full load
Output current ripple LF	≤ 4	%	Ripple = peak / average, < 3kHz
Output P _{st} ^{LM}	≤ 0.1		
Output SVM	≤ 0.3		
Output power	17.0...50.0	W	

Control interfaces

Specification item	Value	Unit	Condition
Control method	Fixed		

Wiring and Connections

Specification item	Value	Unit	Type
Input wire cross-section	0.75...2.5 / 18...14	mm ² / AWG	solid / stranded wire
Input wire strip length	10...11	mm	
Output wire cross-section	0.5...1.5 / 20...16	mm ² / AWG	solid / stranded wire
Output wire strip length	8.5...9.5	mm	
Maximum cable length	0.6	m	Total length of wiring including LED module, one way
Loop Through	Input		




Isolation

Insulation per IEC61347-1	Input	Output+LEDset
Input	-	SELV
Output+LEDset	SELV	-

Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	200	mm	
Mounting hole distance (A2)	99.5	mm	
Length (A3)	123	mm	
Width (B1)	75	mm	
Width (B2)	64.5	mm	
Height (C1)	32	mm	
Mounting hole diameter (D1)	4.1	mm	
Mounting hole diameter (D2)	4.1	mm	
Weight	217	gram	




Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20...+50	°C	Higher ambient temperature allowed as long as Tcase-max is not exceeded
Tcase-max	85	°C	Maximum temperature measured at Tcase-point
Tcase-life	75	°C	Measured at Tcase-point
Maximum housing temperature	110	°C	In case of a failure, inherent by design
Relative humidity	10...90	%	Non-condensing

Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	50,000	hours	Measured temperature at Tcase-point is Tcase-life. Maximum failures = 10%
Driver lifetime Tcmax	0	hours	Measured temperature at Tcase-point is Tcase-life. Maximum failures = 10%



Maximum failures = 10%

Temperature [°C]	Lifetime	Unit	Condition
85	25000	hr	Temperature measured @Tc point
80	35000	hr	
75	50000	hr	
70	>50000	hr	
65	>50000	hr	

Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25...+85	°C	Non-condensing
Relative humidity	5...95	%	

Programmable features


Specification item	Available	Default setting	Condition
Set Adjustable Output Current (AOC)	LEDset, SimpleSet	700 mA	If the output current is set via LEDset, do not leave open / short-circuit. See Design-In Guide for resistor value table.
DC emergency (DCemDim)	No		With a DC mains the output current is 100%. (EOFi)

Non-programmable features

Specification item	Value	Condition
Open load protection	Yes	Automatic recovering
Short circuit protection	Yes	Automatic recovering
Over power protection	Yes	Automatic recovering
Hot wiring	No	
Suitable for fixtures with protection class	I and II	per IEC60598

Inrush current

Specification item	Value	Unit	Condition
Inrush current	8.9	A	Input voltage 230V
Inrush peak width	20	µs	Input voltage 230V, measured at 50% height
Drivers / MCB 16A type B @230V AC	≤ 24	pcs	Input voltage 230V



Please refer to the driver design in guide if you use other MCB-types.

If several mini circuit breakers are used directly side-by-side (without distance piece) a correction factor of 80% has to be applied to the rated current

Driver touch current / protective conductor current / earth leakage current

Specification item	Value	Unit	Condition
Typical Touch Current (ins. Class II)	0.7	mA peak	Acc. IEC61347-1. LED module contribution not included

Surge immunity


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	L-N acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	2	kV	L/N - GND acc. IEC61000-4-5. 12 Ohm, 1.2/50us, 8/20us

Application Info (Approbation)

Specification item	Value
Approval marks and Certifications	CCC / CE / EL / ENEC / SELV
Ingress Protection classification (IP)	20
Application	Indoor Point
Mounting Type	Built-in / Independent


Graphs

Operating window




Type	Output current (mA)	Min. output voltage (V)	Max. output voltage (V)	Max. output power (W)
Xitanium 50W WH 0.7-1.5A 54V Is G2	700	24	54	37.8
Xitanium 50W WH 0.7-1.5A 54V Is G2	750	24	54	40.5
Xitanium 50W WH 0.7-1.5A 54V Is G2	800	24	54	43.2
Xitanium 50W WH 0.7-1.5A 54V Is G2	850	24	54	45.9
Xitanium 50W WH 0.7-1.5A 54V Is G2	900	24	54	48.6
Xitanium 50W WH 0.7-1.5A 54V Is G2	950	24	52	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1000	24	50	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1050	24	47	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1100	24	45	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1150	24	43	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1200	24	41	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1250	24	40	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1300	24	38	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1350	24	37	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1400	24	35	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1450	24	34	50
Xitanium 50W WH 0.7-1.5A 54V Is G2	1500	24	33	50


Power factor versus output power



Efficiency versus output power



THD versus output power



Notes

Max. numbers of drivers for Loop through ≤ 24 PCS at the rated input voltage range.