



中国国家强制性产品认证证书

证书编号: 2019011002186538

委托人名称、地址

昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

生产者(制造商)名称、地址

昕诺飞(中国)投资有限公司
上海市闵行区田林路888弄9号楼

生产企业名称、地址

昕诺飞电子(厦门)有限公司
厦门市云顶北路2000号

产品名称和系列、规格、型号

LED模块用交流电子控制装置(整体式,恒流模式,安全特低电压)
见附件:220-240V 50/60Hz。

产品标准和技术要求

GB17625.1-2012;GB/T17743-2017;GB19510.1-2009;GB19510.14-2009

上述产品符合强制性产品认证实施规则 CNCA-C10-01:2014 的要求,
特发此证。

发证日期:2019年05月22日 有效期至:2024年05月22日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询



主任:

陆楠



中国质量认证中心



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2019011002186538

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE FACTORY

Signify Electronics (Xiamen) Co., Ltd.
No.2000 North Yunding Road, Xiamen, Fujian Province, P.R. China

PRODUCT NAME, MODEL AND SPECIFICATION

A.C. Supplied Electronic Controlgear For LED Modules (Integral, Constant Current Mode, SELV)

See Appendix; 220-240V 50/60Hz.

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB17625.1-2012;GB/T17743-2017;GB19510.1-2009;GB19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO.CNCA-C10-01:2014).

Valid from: May.22,2019

Valid until: May.22,2024

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through CNCA's website: www.cnca.gov.cn



President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

<http://www.cqc.com.cn>

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666

Q 2301487



中国国家强制性产品认证证书

附 录

第 1 页 共 1 页

证书编号: 2019011002186538

纸 号: 2301487

Xitanium 42W/a 0.9/1.05A 40V 3C 230V PCB

输出: 42W 第一路: 0.9A 60Vdcmax, 第二路: 1.05A 60Vdcmax

Xitanium 32W/a 0.7/0.8A 40V 3C 230V PCB

输出: 32W 第一路: 0.7A 60Vdcmax, 第二路: 0.8A 60Vdcmax

Xitanium 30W/a 0.6/0.75A 40V 3C 230V PCB

输出: 30W 第一路: 0.6A 60Vdcmax, 第二路: 0.75A 60Vdcmax

Xitanium 42W/a 0.9/1.05A 40V 1C 230V PCB

输出: 42W 第一路: 0.9A 60Vdcmax, 第二路: 1.05A 60Vdcmax

Xitanium 32W/a 0.7/0.8A 40V 1C 230V PCB

输出: 32W 第一路: 0.7A 60Vdcmax, 第二路: 0.8A 60Vdcmax

Xitanium 30W/a 0.6/0.75A 40V 1C 230V PCB

输出: 30W 第一路: 0.6A 60Vdcmax, 第二路: 0.75A 60Vdcmax

以上均为输入: 220-240V 50/60Hz。

注: 此附录与证书同时使用时有效。



主 任:

陆 楠



中国质量认证中心