



# Certificate of Conformity

Global-Mark Pty. Ltd., certify the electrical equipment described hereunder complies with standards listed herein and authorises the certificate holder to affix the mentioned mark to products of the same type; or the Regulatory Compliance Mark (RCM) provided that the requirements of all relevant parts of AS/NZS 4417 applicable to the article are fulfilled. In placing the authorised mark on the product, the certificate holder makes a declaration of compliance with the certification standard(s) and confirms that the product is identical to the product certified herein.

CERTIFICATION AND CERTIFICATE HOLDER DETAILS			
Company Name	<b>Signify Netherlands B.V</b>		
Address	<b>High Tech Campus 48 Eindhoven - 5656 AE Netherlands</b>		
Client ID	<b>105985</b>	Global-Mark File Number:	<b>105985-003</b>
Certification and Authorized Mark Number	<b>GMA-505182-EA</b>	System 1 Approval	
Certification Standard(s)	<b>AS 61347.2.13:2018 Lamp Control Gear - Part 2-13: Particular Requirements For D.C Or A.C Supplied Electronic Control Gear For Led Modules.</b>		Revision Number <b>01</b>
Type of Certification	<b>Electrical Safety Product</b>	<b>Scheme</b>	<b>Global-Mark Electrical Product Safety Certification Scheme</b>

CERTIFICATE DATES	
Certificate Issue Date	<b>9/04/2019</b>
Certificate Last Update Date	<b>11/04/2019</b>
Certification Expiry Date	<b>9/04/2024</b>

This certification remains valid until the above mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate of Conformity remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to [www.jas-anz.org/register](http://www.jas-anz.org/register) for verification.



Certification Manager

**JAS-ANZ**



[Global-Mark.com.au](http://Global-Mark.com.au)®



global-mark®

# Certificate of Conformity

CERTIFIED ELECTRICAL EQUIPMENT				
Declared Article	Product Description	Trade Name	Model Number	Rating
Power Supply or Charger	LED driver	PHILIPS	Xitanium 10W/a 0.2/0.25A 40V 3CB 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,065 A; Pin: 13 W; PF: 0,9C; Iout: 0,2/0,25 A; Pout: 8/10 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 10W/a 0.2/0.25A 40V 3CG 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,065 A; Pin: 13 W; PF: 0,9C; Iout: 0,2/0,25 A; Pout: 8/10 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 10W/a 0.2/0.25A 40V 3CW 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,065 A; Pin: 13 W; PF: 0,9C; Iout: 0,2/0,25 A; Pout: 8/10 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 20W/a 0.35/0.5A 40V 3CB 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,12 A; Pin: 25 W; PF: 0,9C; Iout: 0,35/0,5 A; Pout: 14/20 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 20W/a 0.35/0.5A 40V 3CG 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,12 A; Pin: 25 W; PF: 0,9C; Iout: 0,35/0,5 A; Pout: 14/20 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 20W/a 0.35/0.5A 40V 3CW 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,12 A; Pin: 25 W; PF: 0,9C; Iout: 0,35/0,5 A; Pout: 14/20 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 30W/a 0.6/0.75A 40V 3CB 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,19 A; Pin: 37 W; PF: 0,9C; Iout: 0,6/0,75 A; Pout: 24/30 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 30W/a 0.6/0.75A 40V 3CG 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,19 A; Pin: 37 W; PF: 0,9C; Iout: 0,6/0,75 A; Pout: 24/30 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 30W/a 0.6/0.75A 40V 3CW 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,19 A; Pin: 37 W; PF: 0,9C; Iout: 0,6/0,75 A; Pout: 24/30 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV

This certification remains valid until the above mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate of Conformity remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to [www.jas-anz.org/register](http://www.jas-anz.org/register) for verification.



Certification Manager

Global-Mark Pty Ltd, Copyright 2012 - 407, 32 Delhi Road, North Ryde NSW 2113, Australia



Global-Mark.com.au®





global-mark®

# Certificate of Conformity

Power Supply or Charger	LED driver	PHILIPS	Xitanium 32W/a 0.7/0.8A 40V 3CB 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,19 A; Pin: 38 W; PF: 0,9C; Iout: 0,7/0,8 A; Pout: 28/32 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 32W/a 0.7/0.8A 40V 3CG 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,19 A; Pin: 38 W; PF: 0,9C; Iout: 0,7/0,8 A; Pout: 28/32 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 32W/a 0.7/0.8A 40V 3CW 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,19 A; Pin: 38 W; PF: 0,9C; Iout: 0,7/0,8 A; Pout: 28/32 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 42W/a 0.9/1.05A 40V 3CB 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,25 A; Pin: 50 W; PF: 0,9C; Iout: 0,9/1,05 A; Pout: 36/42 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 42W/a 0.9/1.05A 40V 3CG 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,25 A; Pin: 50 W; PF: 0,9C; Iout: 0,9/1,05 A; Pout: 36/42 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV
Power Supply or Charger	LED driver	PHILIPS	Xitanium 42W/a 0.9/1.05A 40V 3CW 230V	Un: 220-240 V; fn: 50/60 Hz; In: 0,25 A; Pin: 50 W; PF: 0,9C; Iout: 0,9/1,05 A; Pout: 36/42 W; Uout: 30-40 Vdc, 60 VdcMAX; Independent; SELV

## RELEVANT TRADEMARK (S)

## COMMENTS OR CONDITIONS ON THE CERTIFICATION

2019/04/11 Modification 1  
 - add alternative models with outputs 24/30W, 28/32W & 36/42W  
 - Classified as "Non IC"

**End of document**

This certification remains valid until the above mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate of Conformity remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to [www.jas-anz.org/register](http://www.jas-anz.org/register) for verification.



Certification Manager

Global-Mark Pty Ltd, Copyright 2012 - 407, 32 Delhi Road, North Ryde NSW 2113, Australia



Global-Mark.com.au®

