Australia and New Zealand Certificate of Suitability- addendum

Certificate
ULL-102210-A1

Issue date
2026-06-09

Expiration date
2031-06-09

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic driver for LED modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability-addendum

Certificate No: ULL-102210-A1
Original Date of Certification: 2021-06-21
Date of Issue/Revision: 2026-06-09

Trade Name or Trademark: PHILIPS, SIGNIFY, ADVANCE, XITANIUM

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared - Commercial (not certified for residential or household use)

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:
Xi LP 110W 0.2-0.7A S1 230V C133 sXt
Uin: 220-240 V, fn: 50/60 Hz, Iin: 0.59-0.49 A,
Iout: 200-700 mA, Pout: 110W, Uout: 70-220 Vdc,
Uout (open-circuit): 300 Vmax, tc(max): 90 °C, PF: 0.95, Built-in

Xi LP 110W 0.3-1.0A S1 230V C133 sXt
Uin: 220-240 V, Fn: 50/60 Hz, Iin: 0.59-0.49 A,
Uout: 50-160 Vdc, Pout: 110W, Iout: 300-1050 mA,
Uout (open-circuit): 230 Vmax, tc(max): 90 °C, PF: 0.95, Built-in

Xi LP 75W 0.2-0.7A S1 230V C133 sXt:
Uin: 220-240 V, fn: 50/60 Hz, Iin:0.4-0.34 A,
Uout: 50-150 Vdc, Pout: 75 W, Iout: 200-700 mA,
Uout (open-circuit): 220 Vmax, tc(max): 80 °C, PF: 0.95,
ta: -40…+55 °C, Pin: 84 W, Built-in

Xi LP 75W 0.3-1.0A S1 230V C133 sXt:
Uin: 220-240 V, fn: 50/60 Hz, Iin: 0.4-0.34 A,
Iout: 300-1050 mA, Pout: 75 W, Uout: 35-108 Vdc,
Uout (open-circuit): 150 Vmax, tc(max): 80 °C, PF: 0.95,
ta: -40…+55 °C,Pin: 84 W, Built-in

Xi LP 75W 0.5-1.5A S1 230V C133 sXt:
Uin: 220-240 V, fn: 50/60 Hz, Iin: 0.4-0.34 A,
Iout: 500-1500 mA, Pout: 75 W, Uout: 25-75 Vdc,
Uout(open-circuit): 120 Vmax, tc(max): 80 °C, PF: 0.95,
ta: -40…+55 °C, Pin: 84 W, Built-in, SELV

Details of addendum :
- Trade names “SIGNIFY”, “XITANIUM”, and “ADVANCE” added.
- Certificate is renewed.

© 2026 UL LLC. All rights reserved.
Form-ULID-013925-CoS - ver 2.0