

Australia and New Zealand Certificate of Suitability

Certificate
ULL-103704

Issue date
2024-12-20

Expiration date
2029-12-20



www.jasanz.org/register

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

LED DRIVER

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018;
AS/NZS 61347.1:2016+A1

ANZ Certification Scheme requirements.



Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

Australia and New Zealand Certificate of Suitability

Certificate No: ULL-103704

Date of Issue/Revision: 2024-12-20

Trade Name or Trademark: PHILIPS

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: None.

Model Details:

Model Name
Xi 75W 0.15-0.7A 220V SR FlexTune 230V
Xi 36W 0.08-0.4A 220V SR FlexTune 230V

Additional Information:

Xi 75W 0.15-0.7A 220V SR FlexTune 230V

Pn: 85 W, Un: 220-240 V, In: 0.4 A, fn: 50/60 Hz, PF: 0.9C,

Un: 186-250 Vdc, In: 0.48-0.33 Adc,

Pout: 75 W, Uout: 50-220 Vdc, 250 Vdc Max, Iout: 0.15-0.7 Adc,

tc: 75°C, ta: -25...+50 °C, Built-in

Xi 36W 0.08-0.4A 220V SR FlexTune 230V

Pn: 42 W, Un: 220-240 V, In: 0.2 A, fn: 50/60 Hz, PF: 0.9C,

Un: 186-250 Vdc, In: 0.23-0.17 Adc,

Pout: 36 W, Uout: 50-220 Vdc, 250 Vdc Max, Iout: 0.08-0.4 Adc,

tc: 75°C, ta: -25...+50 °C, Built-in