

Certificate of Suitability

Global-Mark Pty. Ltd., certify the electrical equipment described hereunder complies with standards listed herein and notifies the certificate holder to affix the Regulatory Compliance Mark (RCM) mark on the product of the same type provided that the requirements of all relevant parts of AS/NZS 4417 applicable to the article are fulfilled. In placing the RCM mark on the product, the Responsible Supplier makes a declaration of compliance with the certification standard(s) and confirms that the product is identical to the product certified herein. This Certificate meets the requirements of a Recognised External Certification Scheme (RECS).

CERTIFICATION AND CERTIFICATE HOLDER DETAILS

Company Name	Signify Netherlands B.V	Other Name	
Address	High Tech Campus 48 Eindhoven - 5656 AE Netherlands		
Client ID	105985	Global-Mark File Number:	105985-083
Certification Number	GMA-514014	Revision Number	00
Certificate Standard(s)	AS 61347.2.13:2018 & AS/NZS 61347.1:2016 + A1 Lamp Control Gear - Part 2-13: Particular Requirements For D.C Or A.C Supplied Electronic Control Gear For Led Modules.		
Type of Certification	Electrical Safety Product	Scheme	Global-Mark Electrical Product Safety Certification Scheme

System 1 Approval

CERTIFICATE DATES

Certificate Issue Date	11/11/2022
Certificate Last Update Date	
Certification Expiry Date	11/11/2027

This certification remains valid until the above mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to www.jas-anz.org/register for verification.



Certification Manager



Global-Mark Pty Ltd, Copyright 2012 - 407, 32 Delhi Road, North Ryde NSW 2113, Australia



Certificate of Suitability

CERTIFIED ELECTRICAL EQUIPMENT				
Declared Article	Product Description	Trade Name	Model Number	Rating
Non declared	LED driver	PHILIPS	Xitanium 35W 0.08-0.35A 220V S21 230V	Uin: 220-240 Vac; Iin: 0,18 Aac; Freq: 50/60 Hz; DC; PF: 0,95; Uin: 186-250 Vdc; Iin: 0,21-0,16 Aac; Pin: 39 W; Output Voltage(range): 50-220 Vdc; Uout: 250 V; Pout: 35 W; Iout: 0,08-0,35 Aac; ta: -25...+50°C; tc: 75°C; Built-in
Non declared	LED driver	PHILIPS	Xitanium 60W 0.08-0.35A 300V S21 230V	Uin: 220-240 Vac; Iin: 0,3 Aac; Freq: 50/60 Hz; DC; PF: 0,96; Uin: 186-250 Vdc; Iin: 0,36-0,27 Aac; Pin: 66 W; Output Voltage(range): 100-300 Vdc; Uout: 330 V; Pout: 60 W; Iout: 0,08-0,35 Aac; ta: -25...+50°C; tc: 75°C; Built-in
Non declared	LED driver	PHILIPS	Xitanium 60W 0.15-0.5A 220V S21 230V	Uin: 220-240 Vac; Iin: 0,31 Aac; Freq: 50/60 Hz; DC; PF: 0,96; Uin: 186-250 Vdc; Iin: 0,36-0,27 Aac; Pin: 67 W; Output Voltage(range): 50-220 Vdc; Uout: 250 V; Pout: 60 W; Iout: 0,15-0,5 Aac; ta: -25...+50°C; tc: 75°C; Built-in
Non declared	LED driver	PHILIPS	Xitanium 90W 0.25-0.7A 220V S21 230V	Uin: 220-240 Vac; Iin: 0,45 Aac; Freq: 50/60 Hz; DC; PF: 0,97; Uin: 186-250 Vdc; Iin: 0,53-0,39 Aac; Pin: 97 W; Output Voltage(range): 50-220 Vdc; Uout: 250 V; Pout: 90 W; Iout: 0,25-0,7 Aac; ta: -25...+50°C; tc: 75°C; Built-in
Non declared	LED driver	PHILIPS	Xitanium 35W 0.08-0.35A 220V 21 230V	Uin: 220-240 Vac; Iin: 0,18 Aac; Freq: 50/60 Hz; DC; PF: 0,95; Uin: 186-250 Vdc; Iin: 0,21-0,16 Aac; Pin: 39 W; Output Voltage(range): 50-220 Vdc; Uout: 250 V; Pout: 35 W; Iout: 0,08-0,35 Aac; ta: -25...+50°C; tc: 75°C; Built-in
Non declared	LED driver	PHILIPS	Xitanium 60W 0.08-0.35A 300V 21 230V	Uin: 220-240 Vac; Iin: 0,3 Aac; Freq: 50/60 Hz; DC; PF: 0,96; Uin: 186-250 Vdc; Iin: 0,36-0,27 Aac; Pin: 66 W; Output Voltage(range): 100-300 Vdc; Uout: 330 V; Pout: 60 W; Iout: 0,08-0,35 Aac; ta: -25...+50°C; tc: 75°C; Built-in

This certification remains valid until the above mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to www.jas-anz.org/register for verification.



Certification Manager



Global-Mark Pty Ltd, Copyright 2012 - 407, 32 Delhi Road, North Ryde NSW 2113, Australia



Certificate of Suitability

Non declared	LED driver	PHILIPS	Xitanium 60W 0.15-0.5A 220V 21 230V	Uin: 220-240 Vac; Iin: 0,31 Aac; Freq: 50/60 Hz; DC; PF: 0,96; Uin: 186-250 Vdc; Iin: 0,36-0,27 Adc; Pin: 67 W; Output Voltage(range): 50-220 Vdc; Uout: 250 V; Pout: 60 W; Iout: 0,15-0,5 Adc; ta: -25...+50°C; tc: 75°C; Built-in
Non declared	LED driver	PHILIPS	Xitanium 90W 0.25-0.7A 220V 21 230V	Uin: 220-240 Vac; Iin: 0,45 Aac; Freq: 50/60 Hz; DC; PF: 0,97; Uin: 186-250 Vdc; Iin: 0,53-0,39 Adc; Pin: 97 W; Output Voltage(range): 50-220 Vdc; Uout: 250 V; Pout: 90 W; Iout: 0,25-0,7 Adc; ta: -25...+50°C; tc: 75°C; Built-in

RELEVANT TRADEMARK (S)

COMMENTS OR CONDITIONS ON THE CERTIFICATION
Nil

End of document

This certification remains valid until the above mentioned expiry date and subject to the organisation's continued compliance with the certification standard, and Global-Mark's Terms and Conditions. This Certificate remains the property of Global-Mark Pty Ltd, Company Number: ACN.108-087-654. The use of the Accreditation Mark indicates accreditation by the Joint Accreditation System of Australia and New Zealand in respect to those activities covered by JAS-ANZ accreditation. Refer to www.jas-anz.org/register for verification.



Certification Manager

Global-Mark Pty Ltd, Copyright 2012 - 407, 32 Delhi Road, North Ryde NSW 2113, Australia

