Ref. Certif. No.

NL-126820

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Electronic controlgear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
When more than one factory	☒ Additional information on page 3
Ratings and principal characteristics	**Product data** Ratings: Xitanium 35W 0.08-0.35A 220V S21 230V: Xitanium 35W 0.08-0.35A 220V 21 230V: Uin: 220-240 Vac; Iin: 0,18 Aac; Freq: 50/60 Hz; DC; PF: 0,95; Uin: 186-250 Vdc; Iin: 0,21-0,16 Adc; Pin: 39 W; Uout: 250 V max; Uoutput: 50-220 Vdc; Prated: 35 W; Irated: 0,08-0,35 Adc; ta: -25…+50°C; tc: 75°C; Built-in Xitanium 60W 0.08-0.35A 300V S21 230V: Xitanium 60W 0.08-0.35A 300V 21 230V: Uin: 220-240 Vac; Iin: 0,3 Aac; Freq: 50/60 Hz; DC; PF: 0,96; Uin: 186-250 Vdc; Iin: 0,36-0,27 Adc; Pin: 66 W; Uout: 330 V max; Uoutput: 100-300 Vdc; Prated: 60 W; Irated: 0,08-0,35 Adc; ta: -25…+50°C; tc: 75°C; Built-in Xitanium 60W 0.15-0.5A 220V S21 230V: Xitanium 60W 0.15-0.5A 220V 21 230V: Uin: 220-240 Vac; Iin: 0,31 Aac; Freq: 50/60 Hz; DC; PF: 0,96; Uin: 186-250 Vdc; Iin: 0,36-0,27 Adc; Pin: 67 W; Uout: 250 V max; Uoutput: 50-220 Vdc; Prated: 60 W; Irated: 0,15-0,5 Adc; ta: -25…+50°C; tc: 75°C; Built-in Xitanium 90W 0.25-0.7A 220V S21 230V: Xitanium 90W 0.25-0.7A 220V 21 230V: Uin: 220-240 Vac; Iin: 0,45 Aac; Freq: 50/60 Hz; DC; PF: 0,97; Uin: 186-250 Vdc; Iin: 0,53-0,39 Adc; Pin: 97 W; Uout: 250 V max; Uoutput: 50-220 Vdc; Prated: 90 W; Irated: 0,25-0,7 Adc; ta: -25…+50°C; tc: 75°C; Built-in
Trademark / Brand (if any)	PHILIPS, SIGNIFY, XITANIUM or ADVANCE

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-15

Signature: May Liu

Ref. Certif. No.

NL-126820

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Xitanium 35W 0.08-0.35A 220V 21 230V, Xitanium 35W 0.08-0.35A 220V S21 230V, Xitanium 60W 0.08-0.35A 300V 21 230V, Xitanium 60W 0.08-0.35A 300V S21 230V, Xitanium 60W 0.15-0.5A 220V 21 230V, Xitanium 60W 0.15-0.5A 220V S21 230V, Xitanium 90W 0.25-0.7A 220V 21 230V and Xitanium 90W 0.25-0.7A 220V S21 230V
Additional information	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: AU, EU Group Differences, NZ
As shown in the Test Report Ref. No. which forms part of this Certificate	6271320.50(A-B) and 6271320.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-15

Signature: May Liu

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Additional factory

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-15

Signature: May Liu