Australia and New Zealand Certificate of Suitability

Certificate
ULL-104587

Issue date
2026-06-30

Expiration date
2031-06-30

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic controlgear for LED modules

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Stuart Foster (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability

Certificate No: ULL-104587
Date of Issue/Revision: 2026-06-30

Trade Name or Trademark: PHILPS, SIGNIFY, XITANIUM, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: Product is a component for building in.

Model Details and Additional Information:
Rating:
Xitanium 35W 0.08-0.35A 220V S21 230V
Uin: 220-240 Vac, Iin: 0.18 Aac, Freq: 50/60 Hz, DC, PF: 0.95,
Uin: 186-250 Vdc, Iin: 0.21-0.16 Adc, Pin: 39 W, Uout: 250 V max,
Uoutput: 50-220 Vdc, Prated: 35 W,
Irated: 0.08-0.35 Adc, ta: -25…+50°C, tc: 75°C, Built-in

Xitanium 60W 0.08-0.35A 300V S21 230V
Uin: 220-240 Vac, Iin: 0.3 Aac, Freq: 50/60 Hz, DC, PF: 0.96,
Uin: 186-250 Vdc, Iin: 0.36-0.27 Adc, Pin: 66 W, Uout: 330 V max,
Uoutput: 100-300 Vdc, Prated: 60 W,
Irated: 0.08-0.35 Adc, ta: -25…+50°C, tc: 75°C, Built-in

Xitanium 60W 0.15-0.5A 220V S21 230V
Uin: 220-240 Vac, Iin: 0.31 Aac, Freq: 50/60 Hz, DC, PF: 0.96,
Uin: 186-250 Vdc, Iin: 0.36-0.27 Adc, Pin: 67 W, Uout: 250 V max,
Uoutput: 50-220 Vdc, Prated: 60 W,
Irated: 0.15-0.5 Adc, ta: -25…+50°C, tc: 75°C, Built-in

Xitanium 90W 0.25-0.7A 220V S21 230V
Uin: 220-240 Vac, Iin: 0.45 Aac, Freq: 50/60 Hz, DC, PF: 0.97,
Uin: 186-250 Vdc, Iin: 0.53-0.39 Adc, Pin: 97 W, Uout: 250 V max,
Uoutput: 50-220 Vdc, Prated: 90 W,
Irated: 0.25-0.7 Adc, ta: -25…+50°C, tc: 75°C, Built-in

Xitanium 35W 0.08-0.35A 220V 21 230V
Uin: 220-240 Vac, Iin: 0.18 Aac, Freq: 50/60 Hz, DC, PF: 0.95,
Uin: 186-250 Vdc, Iin: 0.21-0.16 Adc, Pin: 39 W, Uout: 250 V max,
Uoutput: 50-220 Vdc, Prated: 35 W,
Irated: 0.08-0.35 Adc, ta: -25…+50°C, tc: 75°C, Built-in

Xitanium 60W 0.08-0.35A 300V 21 230V
Uin: 220-240 Vac, Iin: 0.3 Aac, Freq: 50/60 Hz, DC, PF: 0.96,
Uin: 186-250 Vdc, Iin: 0.36-0.27 Adc, Pin: 66 W, Uout: 330 V max,
Uoutput: 100-300 Vdc, Prated: 60 W,
Irated: 0.08-0.35 Adc, ta: -25…+50°C, tc: 75°C, Built-in

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability

Certificate No: ULL-104587
Date of Issue/Revision: 2026-06-30

Xitanium 60W 0.15-0.5A 220V 21 230V
Uin: 220-240 Vac, Iin: 0.31 Aac, Freq: 50/60 Hz, DC, PF: 0.96,
Uin: 186-250 Vdc, Iin: 0.36-0.27 Adc, Pin: 67 W, Uout: 250 V max,
Uoutput: 50-220 Vdc, Prated: 60 W,
Irated: 0.15-0.5 Adc, ta: -25…+50°C, tc: 75°C, Built-in

Xitanium 90W 0.25-0.7A 220V 21 230V
Uin: 220-240 Vac, Iin: 0.45 Aac, Freq: 50/60 Hz, DC, PF: 0.97,
Uin: 186-250 Vdc, Iin: 0.53-0.39 Adc, Pin: 97 W, Uout: 250 V max,
Uoutput: 50-220 Vdc, Prated: 90 W,
Irated: 0.25-0.7 Adc, ta: -25…+50°C, tc: 75°C, Built-in

© 2026 UL LLC. All rights reserved.