



CorePro LED tube Universal T8



CorePro LEDtube UN 1500mm HO 23W830 T8

CorePro, LEDtube, T8, Universal, 1500 mm, 23 W, 58W TL-D, 3000 K, 2500 lm, CRI 80, 50000 hour(s)

The new Philips CorePro LEDtube Universal T8 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips CorePro LEDtube Universal T8 directly fits in luminaires operating either on Electro Magnetic ballasts or HF Electronic ballasts or mains power connection. So simple to operate and no need to carry double stock of products! Perfectly safe, reliable & easy to install Philips CorePro LEDtube Universal T8 is the ideal alternative to standard fluorescent tubes to save energy and lower investment.

Product data

General Information		Correlated Color Temperature (Nom)	
Cap-Base	G13		3000 K
Nominal lifetime	50,000 hour(s)	Luminous Efficacy (rated) (Nom)	108 lm/W
Switching Cycle	50,000	Color Consistency	<6
Lighting Technology	LEDtube	Color rendering index (CRI)	80
Flux measurement reference	Sphere	LLMF At End Of Nominal Lifetime (Nom)	70 %
Warranty period	3 years	Photobiological safety according to EN 62471	RG0
Light Technical		Operating and Electrical	
Color Code	830 [CCT of 3000K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	240 degree(s)	Input Frequency	50 to 60 Hz
Luminous Flux	2,500 lm	Power Consumption	23 W
Color Designation	White (WH)	Lamp Current (Nom)	130 mA
		Starting Time (Nom)	0.5 s

CorePro LED tube Universal T8

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	58W TL-D
Inrush current at mains	9.6
Max. lamp no. on MCB B type 10A – Mains	80
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	80
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	16
Max. lamp no. on MCB B type 16A – Mains	128
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	128
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	25
Ballast Compatibility	Universal

Temperature

T-Case Maximum (Nom)	60 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,500 mm
Bulb Shape	T8
Net Weight (Piece)	0.270 kg

Approval and Application

Energy Efficiency Class	F
-------------------------	---

Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	23 kWh
EPREL Registration Number	1936623
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM) – Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data

Order product name	CorePro LEDtube UN 1500mm HO 23W830 T8
Full product name	CorePro LEDtube UN 1500mm HO 23W830 T8
Full product code	871869680172700
Order code	929001869502
Material Nr. (12NC)	929001869502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696801727
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696801734


Dimensional drawing




Product	D1	D2	A1	A2	A3
CorePro LEDtube UN 1500mm HO 23W830 T8	27.9 mm	28 mm	1,500 mm	1,505.9 mm	1,514.2 mm

CorePro LED tube Universal T8


Photometric data



Spectral Power Distribution Colour - CorePro LEDtube UN 1500mm HO 23W830 T8




General uniform lighting - CorePro LEDtube UN 1500mm HO 23W830 T8




Light Distribution Diagram - CorePro LEDtube UN 1500mm HO 23W830 T8

Lifetime



Lumen Maintenance Diagram - CorePro LEDtube UN 1500mm HO 23W830 T8



Life Expectancy Diagram

CorePro LED tube Universal T8

Lifetime



LifetimeVsTc

FailureRate



Lumen Maintenance Diagram - CorePro LEDtube UN 1500mm HO 23W830 T8

