



Contractor-grade InstantFit (UL Type-A) T8

16T8/LED/48-840/IF18/G 25/1

Contractor grade, LEDtube, T8, 1200 mm, 16 W, 4000 K, 1800 lm, 36000 hour(s)

The InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect. Other lamps claim compatibility but only InstantFit (UL Type A) has been proven to work with over 350 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy the InstantFit lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

Product data

General Information		Light Technical	
Cap-Base	G13	Beam Angle (Nom)	220 degree(s)
Nominal lifetime	36,000 hour(s)	Luminous Flux	1,800 lm
Switching Cycle	50,000	Color Designation	Cool White (CW)
Lighting Technology	LEDtube	Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	112.00 lm/W
		Color Consistency	<6
		Color rendering index (CRI)	80
Color Code	840 [CCT of 4000K]		

Contractor-grade InstantFit (UL Type-A) T8

LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	20K to 120K Hz
Input Frequency	20K to 120K Hz
Power Consumption	16 W
Lamp Current (Max)	330 mA
Lamp Current (Min)	110 mA
Wattage Equivalent	32 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277, 347 V
UL Type	UL Type A
Temperature	
T-Case Maximum (Nom)	35 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass

Product Length	1,200 mm
Bulb Shape	T8
Net Weight (Piece)	0.215 kg

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C


Application Conditions

can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data

Order product name	16T8/LED/48-840/IF18/G 25/1
Full product name	16T8/LED/48-840/IF18/G 25/1
Order code	929001960604
Material Nr. (12NC)	929001960604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677542085
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677542080



Dimensional drawing



Product	D1	D2	A1	A2	A3
16T8/LED/48-840/IF18/G 25/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm


Contractor-grade InstantFit (UL Type-A) T8

Photometric data





Accent Lighting Spots - 16T8/LED/48-840/IF18/G 25/1

Light Distribution Diagram - 16T8/LED/48-840/IF18/G 25/1



Spectral Power Distribution Colour - 16T8/LED/48-840/IF18/G 25/1

Lifetime





LEDtubes 1200mm T8 120-277 16W 1800lm 4000K

LEDtubes 1200mm T8 120-277 16W 1800lm 4000K


Contractor-grade InstantFit (UL Type-A) T8

Lifetime



Lumen Maintenance Diagram - 16T8/LED/48-840/IF18/G 25/1

LEDtubes 1200mm T8 120-277 16W 1800lm 4000K



Lumen Maintenance Diagram - 16T8/LED/48-840/IF18/G 25/1

