



# TrueForce LED Public (Urban/Road – HPL/SON)



## TForce LED HPL ND 40-28W E27 840

MASTER, LED HPL, Corn cob, EM/Mains, 28 W, HPL 80W, SON 70W, E27, 4000 K, 4000 lm, CRI 80, 50000 h

Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. These post-top lamps bring the energy efficiency and long lifetime benefits of LED-to-HID replacement, delivering instant savings for a low initial investment. With the right lamp size and light distribution, customers can easily retrofit TrueForce LED lamps into their existing HPL and SON system, thereby enhancing the light quality with LED HID, without having to change the fixtures or sacrifice the light effect.

### Warnings and Safety

- Installation should always be performed by a qualified electrician or installer. Use the installation guide for instructions
- <https://www.assets.signify.com/is/content/Signify/phl-led-hid-eu-compatibility-list-professional>

### Product data

General Information		Warranty period	
Cap base	E27	8 years	
Nominal lifetime	50,000 h	Light Technical	
Switching Cycle	50,000	Colour Code	840 [CCT of 4000K]
Lighting Technology	LED HPL	Beam angle (nom.)	360 degree(s)
Flux measurement reference	Sphere	Luminous Flux	4,000 lm
		Colour designation	Cool White (CW)

## TrueForce LED Public (Urban/Road – HPL/SON)

Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	142 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Photobiological safety according to EN 62471	RG1

### Operating and Electrical

Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	28 W
Lamp current (nom.)	125 mA
Starting time (nom.)	0.45 s
Warm-up time to 60% light	0.45 s
Power Factor (Fraction)	0.95
Voltage (nom.)	220-240 V
Inrush current at mains	4.6
Max. lamp no. on MCB B type 10A – Mains	47
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	47
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	8
Max. lamp no. on MCB B type 16A – Mains	74
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	74
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	14
Wattage Equivalent (LED HID only)	HPL 80W, SON 70W
Ballast Compatibility	EM/Mains

### Temperature

T-Case maximum (nom.)	60 °C
-----------------------	-------

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Lamp Finish	Clear
Bulb material	Plastic
Bulb shape	Corn cob
Net Weight (Piece)	0.365 kg


### Approval and Application

Energy Efficiency Class	D
Energy-saving product	Yes
Energy consumption kWh/1,000 hours	28 kWh
EPREL Registration Number	403571
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM)	1
Stroboscopic effect	1.6
Ambient temperature range	-30 to +45 °C

### Product Data

Order product name	TForce LED HPL ND 40-28W E27 840
Full product name	TForce LED HPL ND 40-28W E27 840
Full EOC	871869963820700
Order code	929002006402
Material no. (12 NC)	929002006402
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699638207
Numerator – packs per outer box	6
EAN/UPC – Case	8718699638214



## Dimensional drawing



Product	D	C
TForce LED HPL ND 40-28W E27 840	75 mm	178 mm


# TrueForce LED Public (Urban/Road – HPL/SON)

## Photometric data




General uniform lighting - TForce LED HPL ND 40-28W E27 840

Light Distribution Diagram - TForce LED HPL ND 40-28W E27 840




Spectral Power Distribution Colour - TForce LED HPL ND 40-28W E27 840

## Lifetime



LEDTrueForce Others 360



Lumen Maintenance Diagram - TForce LED HPL ND 40-28W E27 840

## TrueForce LED Public (Urban/Road – HPL/SON)

