



TrueForce - LED HID HPL



TForce LED HPL ND 60-42W E40 840

MASTER, LED HPL, Corncob, EM/Mains, 42 W, HPL 125W, SON 70W, E40, 4000 K, 6000 lm, CRI 80, 50000 hour(s)

Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) and High Pressure Sodium (SON) lamps. These post-top lamps bring the energy efficiency and long lifetime benefits of LED to HID replacement, delivering instant savings for a low initial investment. With the right lamp size and light distribution, customers can easily retrofit TrueForce LED lamps into their existing HPL and SON system, thereby enhancing the light quality with LED HID, without having to change the fixtures or sacrifice the light effect.

Warnings and Safety

- Installation should always be performed by a qualified electrician or installer. Use the installation guide for instructions
- <https://www.assets.signify.com/is/content/Signify/phl-led-hid-eu-compatibility-list-professional>

Product data

General Information			
Cap-Base	E40	Beam Angle (Nom)	360 degree(s)
Nominal lifetime	50,000 hour(s)	Luminous Flux	6,000 lm
Switching Cycle	50,000	Color Designation	Cool White (CW)
Lighting Technology	LED HPL	Correlated Color Temperature (Nom)	4000 K
Flux measurement reference	Sphere	Luminous Efficacy (rated) (Nom)	142 lm/W
Warranty period	8 years	Color Consistency	<6
		Color rendering index (CRI)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
		Photobiological safety according to EN 62471	RG1
Light Technical			
Color Code	840 [CCT of 4000K]		

TrueForce - LED HID HPL

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	42 W
Lamp Current (Nom)	186 mA
Starting Time (Nom)	0.45 s
Warm-up time to 60% light	0.45 s
Power Factor (Fraction)	0.95
Voltage (Nom)	220-240 V
Inrush current at mains	6.3
Max. lamp no. on MCB B type 10A - Mains	30
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	30
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	7
Max. lamp no. on MCB B type 16A - Mains	48
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	48
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	11
Wattage Equivalent (LED HID only)	HPL 125W, SON 70W
Ballast Compatibility	EM/Mains

Temperature

T-Case Maximum (Nom)	65 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

Bulb Material	Plastic
Bulb Shape	Corncob
Net Weight (Piece)	0.500 kg


Approval and Application

Energy Efficiency Class	D
Energy Saving Product	Yes
Energy Consumption kWh/1000 h	42 kWh
EPREL Registration Number	403606
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1.6
Ambient temperature range	-30 to +45 °C

Product Data

Order product name	TForce LED HPL ND 60-42W E40 840	
Full product name	TForce LED HPL ND 60-42W E40 840	
Full product code	871869963828300	
Order code	929002006802	
Material Nr. (12NC)	929002006802	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8718699638283	
Numerator - Packs per outer box	6	
EAN/UPC - Case	8718699638290	


Dimensional drawing




Product	D	C
TForce LED HPL ND 60-42W E40 840	84 mm	191 mm

TrueForce - LED HID HPL


Photometric data



General uniform lighting - TForce LED HPL ND 60-42W E40 840




Spectral Power Distribution Colour - TForce LED HPL ND 60-42W E40 840




Light Distribution Diagram - TForce LED HPL ND 60-42W E40 840

Lifetime



LEDTrueForce Others 360



Lumen Maintenance Diagram - TForce LED HPL ND 60-42W E40 840

TrueForce - LED HID HPL

