



LED Small Spots

4GU10/LED/927-22/F35/G/WG/T20 10/1

MasterClass, LEDspot, MR16, 50 W, GU10, 2700 K, 2200 K, 380 lm, 25000 hour(s), Glass

MasterClass, LEDspot, MR16, 50 W, GU10, 2700 K, 2200 K, 380 lm, 25000 hour(s), Glass, 95 lm/W

Product data

General Information	
Cap-Base	GU10
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	927-922 [CCT of 2700K-2200K]
Beam Angle (Nom)	35 degree(s)
Luminous Flux	380 lm
Luminous Intensity (Nom)	600 cd
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700 2200 K
Luminous Efficacy (rated) (Nom)	95 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	4 W
Lamp Current (Nom)	50 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	78 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	MR16
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.042 kg

LED Small Spots

Approval and Application

Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-20 to +45 °C

Application Conditions


can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Product Data

Order product name	4GU10/LED/927-22/F35/G/WG/T20 10/1
--------------------	------------------------------------



Full product name	4GU10/LED/927-22/F35/G/WG/T20 10/1
Order code	929002055304
Material Nr. (12NC)	929002055304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677471569
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677471564

Dimensional drawing



Product	D	C
4GU10/LED/927-22/F35/G/WG/T20 10/1	50 mm	54 mm

Photometric data




Accent Lighting Spots - 4GU10/LED/927-22/F35/G/WG/T20 10/1

Light Distribution Diagram - 4GU10/LED/927-22/F35/G/WG/T20 10/1

LED Small Spots

Photometric data



Spectral Power Distribution Colour - 4GU10/LED/927-22/F35/G/WG/T20 10/1

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 4GU10/LED/927-22/F35/G/WG/T20 10/1

