



中国国家强制性产品认证证书

证书编号: 2019011002214501

发证日期: 2023年02月15日

有效期至: 2024年08月06日

认证委托人名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

产品生产者名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产企业名称
及生产地址

产品名称和系列、规格、型号 LED 模块用交直流电子控制装置(LED控制装置, 内装式, 恒流模式, 安全特低电压, ta:50°C, tc:80°C, 控制端口调光, 定温热保护: 110°C)
见附件。220-240V~ 50/60Hz; 186-250VDC

产品标准和技术要求 GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2019年08月06日

经中国合格评定国家认可委员会认可 CNAS C001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2019011002214501

Valid from: Feb.15,2023

Valid until: Aug.06,2024

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND LOCATION
OF THE FACTORY**



PRODUCT MODEL(S)

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (Built-in, Constant Current Mode, SELV,
ta:50°C, tc:80°C, Controlled Port Dimming, Temperature Declared Thermally Protected:110°C)
See Appendix. 220-240V ~ 50/60Hz; 186-250VDC

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Aug.06,2019

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

证书编号 2019011002214501

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3171820

序号	产品型号	参数	调光方式
1	XITANIUM 36W/m 0.3-1.05A 54V S TD 230V	输出: Uout=60V $\overline{\sim}$,1.05A (恒流), 配套光源: Max.36W LED 模块	DALI 调光
2	XITANIUM 36W/m 0.3-1.05A 54V CD 230V	输出: Uout=60V $\overline{\sim}$,1.05A (恒流), 配套光源: Max.36W LED 模块	蓝牙调光
3	XITANIUM 36W/m 0.3-1.05A 54V S TD 230V 9290 034 230	输出: Uout=60V $\overline{\sim}$,1.05A (恒流), 配套光源: Max.36W LED 模块	DALI 调光/NFC 调光
输入: 220-240V $\sim$ 、50/60Hz,调光方式: DALI 调光, 调光范围: 0-100%, tc=80°C,SELV,  ,  , 内装式			
注: 铭牌上186-250Vdc, 特指应急照明的输入; CCC认证只涉及220-240V $\sim$ 。			



中国质量认证中心

