Ref. Certif. No.

NL-127049

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	LED Driver
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
When more than one factory	☐ Additional information on page 2
Ratings and principal characteristics	**Product data** Ratings: 1) Xi SR 75W 0.2–0.7A SNEMP 230V S240 sXt: Pin: 82W; Uin: 220-240V~; Iin: 0,38-0,34A~; fn: 50/60Hz; PF: 0,95; Uin: 186-250Vdc; Iin: 0,3-0,04Adc; Pout: 75W; output voltage: 50-150Vdc, Uout: 200Vmax; Iout: 200-700mA; Isr: 52-60 mA; ta: -40…+55°C; tc(max): +80°C; Built-in 2) Xi SR 75W 0.3–1.0A SNEMP 230V S240 sXt: Pin: 82W; Uin: 220-240V~; Iin: 0,38-0,34A~; fn: 50/60Hz; PF: 0,95; Uin: 186-250Vdc; Iin: 0,3-0,04Adc; Pout: 75W; output voltage: 35-108Vdc, Uout: 150Vmax; Iout: 300-1050mA; Isr: 52-60 mA; ta: -40…+55°C; tc(max): +80°C; Built-in 3) Xi SR 150W 0.2–0.7A SNEMP 230V S240 sXt: Pin: 162W; Uin: 220-240V~; Iin: 0,76-0,67A~; fn: 50/60Hz; PF: 0,95; Uin: 186-250Vdc; Iin: 0,6-0,07Adc; Pout: 150W; output voltage: 90-283Vdc, Uout: 350Vmax; Iout: 200-700mA; Isr: 52-60 mA; ta: -40…+55°C; tc(max): +85°C; Built-in 4) Xi SR 150W 0.3–1.0A SNEMP 230V S240 sXt: Pin: 162W; Uin: 220-240V~; Iin: 0,76-0,67A~; fn: 50/60Hz; PF: 0,95; Uin: 186-250Vdc; Iin: 0,6-0,07Adc; Pout: 150W; output voltage: 70-214Vdc, Uout: 260Vmax; Iout: 300-1050mA; Isr: 52-60 mA; ta: -40…+55°C; tc(max): +85°C; Built-in
Trademark / Brand (if any)	SIGNIFY, XITANIUM, ADVANCE or PHILIPS
Customer's Testing Facility (CTF) Stage used	CTF Stage 3

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-23

Signature: May Liu

Ref. Certif. No.

NL-127049

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Model / Type Ref.	Xi SR 150W 0.2–0.7A SNEMP 230V S240 sXt, Xi SR 150W 0.3–1.0A SNEMP 230V S240 sXt, Xi SR 75W 0.2–0.7A SNEMP 230V S240 sXt and Xi SR 75W 0.3–1.0A SNEMP 230V S240 sXt
Additional information	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	6271424.50 and 6271424.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-06-23

Signature: May Liu