Australia and New Zealand Certificate of Suitability- addendum

Certificate
ULL-101787-A2

Issue date
2026-06-24

Expiration date
2030-04-23

JAS-ANZ

www.jasanz.org/register

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

LED Drivers

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Amarjit Singh (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability-addendum

Certificate No: ULL-101787-A2
Original Date of Certification: 2020-06-18
Date of Issue/Revision: 2026-06-24

Trade Name or Trademark: PHILIPS, SIGNIFY, XITANIUM, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: None

Model Details and Ratings:

1) Xi SR 75W 0.2–0.7A SNEMP 230V S240 sXt:
Pin: 82W, Uin: 220-240V~, Iin: 0.38-0.34A~, fn: 50/60Hz DC, PF: 0.95,
Uin: 186-250Vdc, Iin: 0.3-0.04Adc, Pout: 75W, Uout: 50-150Vdc.
200Vmax, Iout: 200-700mA, Isr: 52-60mA, ta: -40…+55°C,
tc: 80°C, Built-in

2) Xi SR 75W 0.3–1.0A SNEMP 230V S240 sXt:
Pin: 82W, Uin: 220-240V~, Iin: 0.38-0.34A~, fn: 50/60Hz DC, PF: 0.95,
Uin: 186-250Vdc, Iin: 0.3-0.04Adc, Pout: 75W, Uout: 35-108Vdc.
150Vmax, Iout: 300-1050mA, Isr: 52-60 mA, ta: -40…+55°C,
tc: 80°C, Built-in

3) Xi SR 150W 0.2–0.7A SNEMP 230V S240 sXt:
Pin: 162W, Uin: 220-240V~, Iin: 0.76-0.67A~, fn: 50/60Hz DC, PF: 0.95,
Uin: 186-250Vdc, Iin: 0.6-0.07Adc, Pout: 150W, Uout: 90-283Vdc.
350Vmax, Iout: 200-700mA, Isr: 52-60mA, ta: -40…+55°C,
tc: 85°C, Built-in

4) Xi SR 150W 0.3–1.0A SNEMP 230V S240 sXt:
Pin: 162W, Uin: 220-240V~, Iin: 0.76-0.67A~, fn: 50/60Hz DC, PF: 0.95,
Uin: 186-250Vdc, Iin: 0.6-0.07Adc, Pout: 150W, Uout: 70-214Vdc.
260Vmax, Iout: 300-1050mA, Isr: 52-60mA, ta: -40…+55°C,
tc: 85°C, Built-in

Details of addendum :
-Trade names " SIGNIFY", " ADVANCE" and " XITANIUM" added.

© 2026 UL LLC. All rights reserved.