



中国国家强制性产品认证证书

证书编号: 2019011002218623

发证日期: 2023年02月09日

有效期至: 2024年08月16日

认证委托人名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

产品生产者名称 Signify Netherlands B.V.
及注册地址 High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产企业名称
及生产地址

产品名称和系列、规格、型号 LED 模块用交直流电子控制装置 (LED 控制装置, 独立式, 恒流模式, 部分型号控制端口调光, 安全特低电压, ta:50°C, tc:80°C, II类, IP20, 适宜直接安装在普通可燃材料表面, 定温热保护: 110°C) 见附件; 220-240V ~ 50/60Hz, 186-250Vdc

产品标准和
技术要求 GB/T 17743-2021; GB 19510.1-2009; GB 19510.14-2009

上述产品符合 CNCA-C10-01:2014 认证规则的要求, 特发此证。

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2019年08月16日

经中国合格评定国家认可委员会认可 CNAS G001-P

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2019011002218623

Valid from: Feb.09,2023

Valid until: Aug.16,2024

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify Netherlands B.V.
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND LOCATION
OF THE FACTORY**



PRODUCT MODEL(S)

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (Independent, Constant Current Mode, Controlled Port Dimming For Some Type, SELV, ta:50°C, tc:80°C, Class II, IP20, Suitable For Direct Mounting On Normally Flammable Material, Temperature Declared Thermally Protected: 110°C) See Appendix;220-240V ~ 50/60Hz, 186-250Vdc

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Aug.16,2019

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE





中国国家强制性产品认证证书

证书编号 2019011002218623

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 3179385

序号	产品型号	参数	调光方式
1	XITANIUM 20W/m 0.15-0.5A 54V S TD 230V	输出: $U_{out}=60V\text{---},0.5A$ (恒流), 配套光源: Max.20W LED 模块	DALI 调光
2	XITANIUM 20W/m 0.15-0.5A 54V CD 230V	输出: $U_{out}=60V\text{---},0.5A$ (恒流), 配套光源: Max.20W LED 模块	蓝牙调光
3	XITANIUM 20W/m 0.15-0.5A 54V I TD 230V	输出: $U_{out}=60V\text{---},0.5A$ (恒流), 配套光源: Max.20W LED 模块	DALI 调光/NFC 调光
输入: 220-240V~、50/60Hz,调光范围: 0-100%, $t_a=-20\sim 50^{\circ}C$, $t_c=80^{\circ}C$, SELV,  ,  ,  , 			
注: 铭牌上186-250Vdc, 特指应急照明的输入; CCC认证只涉及220-240V~。			



中国质量认证中心





中国国家强制性产品认证证书

变更结论 Modification Approval

证书编号 Certificate No. : 2019011002218623

申请编号 Application No. : A2022CCC1002-4032241

申请人(委托人) Applicant: Signify Netherlands B.V. / Signify Netherlands B.V.

证书编号 Certificate No.(变更前 Original): 2019011002218623

变更产品名称: LED 模块用交直流电子控制装置(LED 控制装置, 独立式, 恒流模式, 部分型号控制端口调光, 安全特低电压, ta:50℃, tc:80℃, II类, IP20, 适宜直接安装在普通可燃材料表面, 定温热保护: 110℃)

Name of Product Modified: A.C. or D.C. Supplied Electronic Controlgear For LED Modules (Independent, Constant Current Mode, Controlled Port Dimming For Some Type, SELV, ta:50℃, tc:80℃, Class II, IP20, Suitable For Direct Mounting On Normally Flammable Material, Temperature Declared Thermally Protected: 110℃)

变更情况 Situation of Modification (见下表 See table below) :

序号	项目 Item	变更前 Original	变更后 Present
1	标准换版	GB/T 17743-2017	GB/T 17743-2021
2	新增型号	见原证书	见变更后证书
3	适用性一致的关键件 变更	见报告: 00501-CG2020-3742	见报告: 00501-CG2020-3742

现批准以上变更。

Above Modification is approved. The present will replace the original.

批准日期(Date): 2023 年 02 月 09 日

第 1 页/共 1 页

签发:

谢肇煦



中国质量认证中心

