



CorePro LED spot MV



CorePro LEDspot 4-50W GU10 827 36D DIM

CorePro, LEDspot, PAR16, 50 W, GU10, 2700 K, 345 lm, CRI 80, 15000 hour(s), Glass

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

Product data

General Information	
Cap-Base	GU10
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Flux measurement reference	Narrow Cone
Warranty period	2 years
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	345 lm
Luminous Intensity (Nom)	700 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	345 lm
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4 W
Lamp Current (Nom)	24 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C

CorePro LED spot MV

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	PAR16
Net Weight (Piece)	0.048 kg

Approval and Application

Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh
EPREL Registration Number	400299
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Ambient temperature range	-20 to +45 °C
---------------------------	---------------


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data


Order product name	CorePro LEDspot 4-50W GU10 827 36D DIM
Full product name	CorePro LEDspot 4-50W GU10 827 36D DIM
Full product code	871869672137700
Order code	929002495902
Material Nr. (12NC)	929002495902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696721377
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696721384

Dimensional drawing




Product	D	C
CorePro LEDspot 4-50W GU10 827 36D DIM	50 mm	54 mm

Photometric data




Light Distribution Diagram - CorePro LEDspot 4-50W GU10 827 36D DIM



Spectral Power Distribution Colour - CorePro LEDspot 4-50W GU10 827 36D DIM


CorePro LED spot MV

Photometric data



Accent Lighting Spots - CorePro LEDspot 4-50W GU10 827 36D DIM

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - CorePro LEDspot 4-50W GU10 827 36D DIM

