



# Essential SmartBright LED Downlight

## DN500B G3 LED9/NW 9W 220V D125 RD

Essential SmartBright LED Downlight, 9 W, 950 lm, 4000 K, Beam angle 110°, White

Essential SmartBright G2 LED Downlight is value for money product with high efficacy, good quality and reliability. It offers multiple configurations from 300lm to 2000lm output, to replace conventional downlight. It can be used for shopping mall, retail store, residential and office. It's an ideal product family to distribute in trade market.

### Product data

General Information		Operating and Electrical	
Light source replaceable	No	Input Voltage	220 to 240 V
Number of gear units	1 unit	Line Frequency	50 or 60 Hz
Driver included	Yes	Input Frequency	50 or 60 Hz
Lighting Technology	LED	Inrush current	2.25 A
Warranty period	3 years	Inrush time	0.101 ms
Light Technical		Power Consumption	9 W
Luminous Flux	950 lm	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	4000 K	Cable	Cable 0.2 m without plug
Luminous Efficacy (rated) (Nom)	105.00 lm/W	Number of products on MCB of 16 A type B	86
Color rendering index (CRI)	80	Suitable for random switching	No
Light source color	840 neutral white	Protection class IEC	Safety class II
Optic type	Beam angle 110°	Controls and Dimming	
Luminaire light beam spread	110°	Dimmable	No
		Driver/power unit/transformer	Power supply unit (On/Off)

# Essential SmartBright LED Downlight

Constant light output	No
-----------------------	----

## Mechanical and Housing

Housing Material	Metal-Plastic
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Matte
Overall length	150 mm
Overall width	150 mm
Overall height	42 mm
Overall diameter	150 mm
Dimensions (Height x Width x Depth)	42 x 150 x 150 mm
Ingress protection code	IP20/40 [Finger-protected;Wire-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	0.160 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(IEC4000K, 0.38, 0.38) < 5SDCM
Power consumption tolerance	+/-10%


## Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.012 %
Median useful life L70B50	30,000 hour(s)

## Product Data


Order product name	DN500B G3 LED9/NW 9W 220V D125 RD
Full product name	DN500B G3 LED9/NW 9W 220V D125 RD
Full product code	692234193555800
Order code	929002677340
Material Nr. (12NC)	929002677340
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341935558
Numerator - Packs per outer box	24
EAN/UPC - Case	6922341935565

## Dimensional drawing




# Essential SmartBright LED Downlight

## Photometric data



General Parameters 4.1 Philips Lighting B.V. Page 117



General uniform lighting - DN500B G3 LED9/NW 9W 220V D125 RD

Light Distribution Diagram - DN500B G3 LED9/NW 9W 220V D125 RD

